





REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
J		REVISED PER ECO-17-011181	03AUG2017	RS	MZ
K		REVISED PER ECO-18-000439	19JAN2018	RS	MZ
L		REVISED PER ECO-20-002045	13FEB2020	RK	MZ

NOTES:

- 1 MATES WITH PLUG 207019-1.
- 2 CIRCUITS 1 THRU 8 COMMONED, 9 THRU 16 COMMONED, 17 THRU 24 COMMONED, 25 THRU 32 COMMONED AND 33 THRU 36 COMMONED TOGETHER.
- 3 ALL CURCUITS COMMONED TOGETHER.
- 4 TIN-LEAD OVER NICKEL PER QQ-N-290 OR COPPER PER MIL-C-14550.
- 5 0.76  $\mu\text{m}$  (.000030) MIN GOLD PER MIL-G-45204 FOR A LENGTH OF 5.08 (.200) FROM MATING END, 3.81  $\mu\text{m}$  (.000150) MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 4.83 (.190) MIN. FROM OPPOSITE END, BOTH OVER 1.27  $\mu\text{m}$  (.000050) MIN NICKEL PER QQ-N-290.
- 6 TIN OVER NICKEL PER QQ-N-290 OR COPPER PER MIL-C-14550.
- 7 0.76  $\mu\text{m}$  (.000030) MIN GOLD PER MIL-G-45204 FOR A LENGTH OF 5.08 (.200) FROM MATING END, 3.81  $\mu\text{m}$  (.000150) MIN TIN PER MIL-T-10727 FOR A LENGTH OF 4.83 (.190) MIN. FROM OPPOSITE END, BOTH OVER 1.27  $\mu\text{m}$  (.000050) MIN NICKEL PER QQ-N-290.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	$\Delta$ 8	(1) 36 POSITION	$\Delta$ 3	1-208062-1
	$\Delta$ 7	(1) 4 POSN AND (4) 8 POSN	$\Delta$ 2	1-208062-0
OBSOLETE	$\Delta$ 6	(1) 36 POSITION	$\Delta$ 3	208062-9
	$\Delta$ 5	(1) 4 POSN AND (4) 8 POSN	$\Delta$ 2	208062-8
OBSOLETE	$\Delta$ 4	(1) 36 POSITION	$\Delta$ 3	208062-7
	$\Delta$ 3	(1) 4 POSN AND (4) 8 POSN	$\Delta$ 2	208062-6
OBSOLETE	$\Delta$ 2	(1) 36 POSITION	$\Delta$ 3	208062-5
	$\Delta$ 1	(1) 4 POSN AND (4) 8 POSN	$\Delta$ 2	208062-4
OBSOLETE	$\Delta$ 0	(1) 36 POSITION	$\Delta$ 3	208062-3
OBSOLETE	$\Delta$ 0	(1) 4 POSN AND (4) 8 POSN	$\Delta$ 2	208062-2
OBSOLETE	$\Delta$ 0	(1) 36 POSITION	$\Delta$ 3	208062-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

FINISH:  $\Delta$ 4/5 BUS TYPE: 36 POSITION, METRIMATE PART NO. 208062-1

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN D.GELTZ 08/13/92	TE Connectivity
0 PLC ± -	1 PLC ± -	CIRK R.STONE 9-21-92	NAME
2 PLC ± ± 0.25[.010]	3 PLC ± -	APVD	PRODUCT SPEC
4 PLC ± -	ANGLES ± -	APVD	APPLICATION SPEC
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT	SIZE CAGE CODE DRAWING NO. RESTRICTED TO
			A1 00779 C=208062
		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV L