



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
B1		ECR-20-004655	01OCT2020	RK SBH

WIRE SCHEDULE
BELEGUNGSPLAN

CONNECTOR	COLOR FARBE
PHASE/+	BROWN/BRAUN
NEUTRAL/-	BLUE/BLAU



NOTES

- 1 PACKAGING:
ASSEMBLIES PACKED IN TE STANDARD BOXES WITH INTERMEDIATE LAYERS OF CORRUGATED PAPER OR PAPER STUFFING. BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
- 2 100% ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.3.1.1

BEMERKUNGEN

- 1 VERPACKUNG:
ASSEMBLIES IN TE STANDARDKARTON MIT ZWISCHENLAGEN (WELLPAPPE ODER PAPIERPÖLSTERKISSEN) VERPACKT. 25 KABEL MIT EINEM GUMMIBAND GEBÜNDELT.
- 2 100% ELEKTRISCHE PRUEFUNG NACH TE SPEZIFIKATION 108-18857.3.1.1

LENGTH SCHEDULE:
Laengentabelle:

	TE Part No.	REV.	LENGTH L (mm)	TOL.	CABLE COLOR
OBSOLETE	1-2083039-1	A	1000	±20	black
	1-2083039-2	B	1000	±20	white
	2-2083039-1	A	1000	±20	black
	2-2083039-2	B	1000	±20	white

OBSOLETE

QTY	QTY	QTY	QTY	DESCRIPTION	ITEM NO.
2	2	1	1	H03VVH2-F 2x0.75mm ² , white	6
1	-	1	-	Cover, white	5
1	1	-	-	6 pos. distributor, yellow LV-2	4
-	see table	-	see table	H03VVH2-F 2x0.75mm ² , black	3
-	1	-	1	Cover, black	2
-	-	1	1	6 pos. distributor, light grey LV-1	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
-	-

DWN	T.BURZYNSKI	27JAN2010
CHK	S.SEDLAKOWA	27JAN2010
APVD	G.LINDEMAN	27JAN2010
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

STE TE Connectivity

NAME
Cable Assembly Mini HVL 6 Way Distri to pigtail

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2083039	-

SCALE NTS SHEET 1 OF 1 REV B1