


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP	11JUN2023	ED	WH



CONN 1
FEMALE STR
CODE Z WATER BLUE
WITHOUT CLIP SLOT
UNSEALED

CONN 2
MALE STR
CODE Z WATER BLUE
WITHOUT CLIP SLOT
UNSEALED

TE P/N	L(mm)	REV
2081377-1	300+10/-0	A
2081377-2	600+10/-0	A
2081377-3	1000+15/-0	A
2081377-4	2000+20/-0	A
2081377-5	3000+30/-0	A
2081377-6	5000+40/-0	A

NOTES:

- ALL RF CONNECTORS MUST BE ASSEMBLED PER MANUFACTURER'S APPLICATION SPECIFICATIONS WITH FOLLOWING [SC]:
1.1: SOCKET CONTACTS CRIMP HEIGHT
1.2: FERRULES' CRIMP HEIGHT
1.3: CONNECTORS TO COAX CABLE RETENTION FORCE
- 100% IN-PROCESS ELECTRICAL TEST:
2.1: DC CONTINUITY, FOR CENTER AND OUTER CONDUCTORS, POINT TO POINT
2.2: SHORT CIRCUITS;
- TEMPERATURE RANGE: -40°C TO 85°C

4. LABEL CONTENT:

TE P/N: XXXXXXXX-X REV: X

DATE: YYYYMMDD

X: FOLLOW DRAWING REVISION

X: -1 OR -2 OR-3

DESCRIPTION:
YYYY: YEAR (EXAMPLE: 2016) MM:
MONTH (EXAMPLE: 02)
DD: DATE (EXAMPLE: 25)

AR	MM	TEAR TAPE FOR PACKAGING	12
1	PC	ID LABEL	11
AR	MM	RG174LL COAXIAL CABLE	10
1	PC	SUBASSY MALE	9
1	PC	CENTER CONTACT MALE	8
1	PC	RETAINER	7
1	PC	FAKRA MALE HSG 1P CADE Z	6
2	PC	OUTER FERRULE	5
1	PC	SUBASSY FEMALE	4
1	PC	CENTER CONTACT FEMALE	3
1	PC	RETAINER	2
1	PC	FAKRA HSG FEMALE 1P CODE Z	1
-X	U/M	DESCRIPTION	ITEM
QTY			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Z.Z.ZHONG 23FEB2023		 TE Connectivity		
		CHK ERIC.DAI 23FEB2023				
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD WENKE.HE 23FEB2023		NAME - FAKRA STR FEMALE TO FAKRA STR MALE WITHOUT CLIP SLOT RG174LL CODE Z
		0 PLC ± -		PRODUCT SPEC		
		1 PLC ± -		—		
		2 PLC ± -		APPLICATION SPEC		
		3 PLC ± -		—		SIZE A2
		4 PLC ± -		CAGE CODE 00779		
MATERIAL -		FINISH -		WEIGHT -		DRAWING NO C=2081377
				CUSTOMER DRAWING		
				SCALE —		SHEET 1 of 1
				REV A		