






LOC	DIST	REV	DATE	BY	CHK	APPV
AD	00	A	09MAY2011	RKC	JE	

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



180X $\varnothing 0.39 \pm 0.05$
 $\varnothing 0.10$
 PLATED THRU HOLE

UNGUIDED
 BACKPLANE HOLE PATTERN
 (CONNECTOR SIDE)





THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: RKC 06MAY2011	TE Connectivity
DIMENSIONS: mm		CHK: J. EABY 06MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPV: J. EABY 06MAY2011	NAME: IMPACT, 5 PAIR, 12 COLUMN, HEADER
0 PLC ±	1 PLC ±0.25	PRODUCT SPEC	UNGUIDED, RIGHT END WALL
2 PLC ±0.13	3 PLC ±	APPLICATION SPEC	SIGNAL MODULE, 0.39 PTH
4 PLC ±	ANGLES ±	WEIGHT	SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO
MATERIAL: SEE TABLE	FINISH: SEE TABLE	CUSTOMER DRAWING	A1100779C=2110194
		SCALE: 5:1	SHEET 1 OF 2 REV A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY . ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTB	DATE	DWN	APVD
AD	00	-	-	SEE SHEET 1	-	-

FINISH	DIM M	PART NUMBER
\triangle_3	5.5	2110194-6
\triangle_3	4.9	2110194-5
\triangle_3	4.5	2110194-4
\triangle_2	5.5	2110194-3
\triangle_2	4.9	2110194-2
\triangle_2	4.5	2110194-1

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	06MAY2011	 TE Connectivity
DIMENSIONS:		CHK	06MAY2011	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	06MAY2011	NAME IMPACT, 5 PAIR, 12 COLUMN, HEADER UNGUIDED, RIGHT END WALL SIGNAL MODULE, 0.39 PTH
	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC	APPLICATION SPEC	
MATERIAL	FINISH	WEIGHT	SIZE	RESTRICTED TO
-	SEE TABLE	-	A100779C=2110194	-
CUSTOMER DRAWING			SCALE	5:1 SHEET 2 OF 2 REV A