

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL RELEASE	10MAR11	GSK	RH
			A1	ECR-12-017258	18JAN13	RK	JK

NOTE:

- WIRING SCHEDULE AS SHOWN
- PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
- ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1
- ASSEMBLIES IN TWO COLORS BLACK AND WHITE

WIRING SCHEDULE

SIDE A	COLOR	SIDE B
F1	BN	F1
F2	RD	F2
F3	OG	F3
F4	BK	F4



	PN	L/m	TOLERANCES/mm
OBSOLETE	X-2083115-1	0.5	+/-3
	X-2083115-2	1	+/-5
	X-2083115-3	1.5	+/-10
	X-2083115-4	2	+/-10
	X-2083115-5	2.5	+/-15

M	L		DESCRIPTION	POS.
M	L	-	CABLE LIYY 4x0.34mm ² WH	4
M	-	L	CABLE LIYY 4x0.34mm ² BK	4
PC	8	8	MICRO QUADLOK SYSTEM SOCKET CONTACT	3
PC	2	2	4 POS. LOW VOLTAGE CONN.F.POSITIONER	2
PC	-	2	4 POS. LOW VOLTAGE REC. CONN.HSG BK	1
PC	2	-	4 POS. LOW VOLTAGE REC. CONN.HSG WH	
UOM	QTY	QTY	DESCRIPTION	POS.
	2--X	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR.G 10MAR11	TE Connectivity														
DIMENSIONS: mm		CHK R.HOSSAINI 10MAR11															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.HOSSAINI 10MAR11	NAME CABLE ASSEMBLY NECTOR S LINE 4 POS., FEMALE TO FEMALE														
<table border="0"> <tr> <td>0 PLC</td><td>± -</td> </tr> <tr> <td>1 PLC</td><td>± -</td> </tr> <tr> <td>2 PLC</td><td>± -</td> </tr> <tr> <td>3 PLC</td><td>± -</td> </tr> <tr> <td>4 PLC</td><td>± -</td> </tr> <tr> <td>ANGLES</td><td>± -</td> </tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC -	SIZE A3		
0 PLC	± -																
1 PLC	± -																
2 PLC	± -																
3 PLC	± -																
4 PLC	± -																
ANGLES	± -																
MATERIAL -		FINISH -	APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C-2083115												
		WEIGHT -	RESTRICTED TO -														
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A1												