




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECO-17-002455	23FEB2017	SY	SY




- NOTES:
- 1 2 CHAMFERS AT INSIDE FOR LOCATION OF REMOVAL TOOL FOR MODULE p.n.216519-1
  - 2 SOLDERPOSTS SUITABLE FOR 0,80 OR 1,0 NOM. DIA HOLES

X	X	X	X	X	X	X	X	X	X	d	ROW
X	X	X	X	X	X	X	X	X	X	b	ROW
X	X	X	X	X	X	X	X	X	X	z	ROW
0	0	0	0	0	0	0	0	0	0	0	POS

AN ASTERISK „X” DENOTES A CONTACT

CONFIRMS TO IEC60603-2 PERFORMANCE LEVEL II REQUIREMENT IN CONTACT AREA Sn OVER Ni IN SOLDER AREA	HOUSING: THERMOPL. POLYESTER G.F. COLOUR: GREY CONTACTS: PHOSPHORBRONZE	216520-4
FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15 NOV.1994 L.V.D.HEIJDEN	 TE Connectivity	
DIMENSIONS: mm		CHK J.V.GUNSVEN		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.V.SOEST	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	3x10 POS. WITH SOLDER POSTS 3x6 POS WITH FEATURE FOR CRIMP-ON, SNAP-IN .	
MATERIAL -		FINISH -	APPLICATION SPEC -	RESTRICTED TO -
		WEIGHT 0.000000	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-216520	REV D
		SCALE -	SHEET 1 OF 1	