



REV.	DATE	BY	CHKD	DESCRIPTION
E3	E-16-017035			
E4	E-17-014128			
E5	E-18-007042			
F	E-20-014964			

- 1 Verpackung siehe Vorschrift V-2112181  
PACKING SEE PACKING INSTRUCTION V-2112181
- 2 100% optischer Test: Lichtausgangsleistung, Receiver-Empfindlichkeit und Status-Pin-Abfrage  
100% OPTICAL TEST: OUTPUT PERFORMANCE, RECEIVER SENSITIVITY AND STATUS-PIN-QUERY
- 3 Massgebend ist nur der deutsche Text  
ONLY THE GERMAN LANGUAGE SHALL BE BINDING
- 4 Alle Masse in () nur als Info  
ALL DIMENSIONS IN () ONLY AS INFO
- 5 Steckersystem gemäss Schnittstelle C-114-18361-1 inklusive Kodierungen  
CONNECTOR ACCORDING TO C-114-18361-1 INCLUDING CODINGS
- 6 Bezugsplan der Stiftreihe  
REFERENCE PIN OF HEADER
- 7 Pinlayout Angaben entsprechen den Form- und Lagertoleranzen der Pins  
(Layout ist entsprechend anzulegen)  
DIMENSIONS RELATE TO SHAPE AND POSITION TOLERANCES OF PINS  
LAYOUT HAS TO BE ADAPTED
- 8 1-2112181-3 wie gezeichnet (Kodierung A)  
1-2112181-3 AS SHOWN (CODING A)
- 9 Gravur der Pins (X-...), Revision (R)  
ENGRAVING OF PINS (X-...), REVISION (R)
- 10 Markierung ZZZ-H03 fuer Diodentyp Hama. L11354-02/S11355-04.  
und Produktionsdatum (DDYY)  
MARKING ZZZ-H03 FOR FOT TYPE HAMA. L11354-02/S11355-04.  
AND DATECODE = (DDYY)
- 11 Pos.7 Staubschutzkappe: Handhabungshilfe  
nicht Teil des endgultigen Produktes  
POS.7 PROTECTION COVER: HANDLING AID  
NOT PART OF FINAL PRODUCT
- 12 Fol-Pins (14x)  
FOT PINS (14x)
- 13 EMV-Schirmblech Pins (13x)  
EMI SHIELD PINS (13x)
- 14 Passend zu Gegenstecker z. B. 1418862 und Leitungssatz  
SUITABLE TO MATING PART E.G. 1418862 AND CONDUCTOR SET
- 15 Gewicht ohne Staubschutzkappe  
WEIGHT WITHOUT DUST COVER
- 16 Pinlayout und max. Baugrösse gemäss C-114-18941-04  
PIN LAYOUT AND MAX. OVERALL SIZE ACC. TO C-114-18941-04
- 17 Bereich fuer Schirmblech-Kontaktierung  
CONTACTING AREA FOR SHIELDING
- 18 Produktmarkierung nach Notizen 09 u. 10 alternativ ueber Etikett moeglich  
PRODUCT MARKING ACC. TO NOTES 09 AND 10 ON STICKER ALTERNATIVELY
- 19 Musterleile mit (ES) markiert  
ENGINEERING SAMPLES MARKED WITH (ES)



Pin Pos	Belegung	ASSIGNMENT
1	/RST	
2	/RST	
3	TXN	
4	TXP	
5	GND_TX	
6	VCC_TX	
7	CInL_TX	
8	STATUS	
9	VCC_RX	
10	GND_RX	
11	RXN	
12	RXP	
13	(VCC_RX2)	
14	VCC_RX2	
EMI-Shield	GND	

PART NO.	PACKAGING	REV.	COD.	DESCRIPTION	QTY.	SURFACE / COLOR	MATERIAL	WEIGHT (g)	VOL. (mm <sup>3</sup> )	POS.	
2-2112181-3	TAPE & REEL	B	A	ASSY GOF WITH SHRINK HOSE	2	TRANSPARENT	Glass / PVDF	0.9	656	7	
				RECEIVER HAMAMATSU S11355-04	1						6
				TRANSMITTER HAMAMATSU L11354-02	1	Au plated	resin and copper alloy				5
				ADAPTER	1	BLACK	PA6/6T-GF25		2898		4
1-2112181-3	TRAY	B	A	ASSY GOF WITH SHRINK HOSE	2	TRANSPARENT	Glass / PVDF	0.9	656	7	
				RECEIVER HAMAMATSU S11355-04	1						6
				TRANSMITTER HAMAMATSU L11354-02	1	Au plated	resin and copper alloy				5
				ADAPTER	1	BLACK	PA6/6T-GF25		2898		4
				EMI SHIELDING	1	TIN HOT DIPPED	CuSn4	7.5	2898	3	
				2 POS. HEADER CODING A	1	BLACK	PA6/6T-GF25			1	

PRODUCT CHARACTERISTICS ACC. QMP EMEA\_12  
 BESONDERE MERKMALE NACH QMP EMEA\_12  
 THIS DRAWING IS A CONTROLLED DOCUMENT.  
 DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
 ALL DIMENSIONS UNLESS OTHERWISE SPECIFIED

0 PLC \*  
 1 PLC \*  
 2 PLC \*  
 3 PLC \*  
 4 PLC \*  
 5 PLC \*

MATERIAL SEE TABLE

TE Connectivity  
 MOST 150 GOF MICRO PIGTAIL FULLY SHIELDED

SCALE: 5:1  
 SHEET 1 OF 1  
 REV F