




LOC		DIST		REVISIONS			
AD	00	P	LTH	DESCRIPTION	DATE	DWN	APVD
		B		HOUSING UPDATE	11AUG2011	RKC	JE





NOTCH DESIGNATES ROW A



- 1. MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2. FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3. FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5. FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH, Ø3.66 DRILL, AND Ø6.5 PAD.
- 6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART ON SHEET 2 FOR OTHER POSITIONS.



LEFT GUIDED BACKPLANE HOLE PATTERN (CONNECTOR SIDE)




1.00 MINIMUM BOARD THICKNESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 04MAY2011	TE Connectivity
DIMENSIONS: mm		CHK J. EARY 04MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EARY 04MAY2011	
0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±		NAME IMPACT, 3 PAIR, 6 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH	
MATERIAL SEE TABLE		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO
FINISH SEE TABLE		APPLICATION SPEC	A100779C=2132528
WEIGHT		CUSTOMER DRAWING	SCALE 6:1 SHEET 1 OF 2 REV B

LOC		DIST		REVISIONS			
AD	00	P	LTN	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1		-	-

	H	5.5	8-2132528-6
	H	4.9	8-2132528-5
	H	4.5	8-2132528-4
	H	5.5	8-2132528-3
	H	4.9	8-2132528-2
	H	4.5	8-2132528-1
	G	5.5	7-2132528-6
	G	4.9	7-2132528-5
	G	4.5	7-2132528-4
	G	5.5	7-2132528-3
	G	4.9	7-2132528-2
	G	4.5	7-2132528-1
	F	5.5	6-2132528-6
	F	4.9	6-2132528-5
	F	4.5	6-2132528-4
	F	5.5	6-2132528-3
	F	4.9	6-2132528-2
	F	4.5	6-2132528-1
	E	5.5	5-2132528-6
	E	4.9	5-2132528-5
	E	4.5	5-2132528-4
	E	5.5	5-2132528-3
	E	4.9	5-2132528-2
	E	4.5	5-2132528-1
	D	5.5	4-2132528-6
	D	4.9	4-2132528-5
	D	4.5	4-2132528-4
	D	5.5	4-2132528-3
	D	4.9	4-2132528-2
	D	4.5	4-2132528-1
	C	5.5	3-2132528-6
	C	4.9	3-2132528-5
	C	4.5	3-2132528-4
	C	5.5	3-2132528-3
	C	4.9	3-2132528-2
	C	4.5	3-2132528-1
	B	5.5	2-2132528-6
	B	4.9	2-2132528-5
	B	4.5	2-2132528-4
	B	5.5	2-2132528-3
	B	4.9	2-2132528-2
	B	4.5	2-2132528-1
	A	5.5	1-2132528-6
	A	4.9	1-2132528-5
	A	4.5	1-2132528-4
	A	5.5	1-2132528-3
	A	4.9	1-2132528-2
	A	4.5	1-2132528-1
	-	5.5	2132528-6
	-	4.9	2132528-5
	-	4.5	2132528-4
	-	5.5	2132528-3
	-	4.9	2132528-2
	-	4.5	2132528-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 04MAY2011	TE Connectivity
DIMENSIONS: mm		CHK J. EARY 04MAY2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EARY 04MAY2011	NAME: IMPACT, 3 PAIR, 6 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH
0 PLC ±0.25		PRODUCT SPEC	
1 PLC ±0.13		APPLICATION SPEC	SIZE: CAGE CODE DRAWING NO. RESTRICTED TO
2 PLC ±		WEIGHT	A100779C=2132528
3 PLC ±		CUSTOMER DRAWING	SCALE 5:1 SHEET 2 OF 2 REV B
ANGLES FINISH SEE TABLE			