








REVISIONS				
P. LTM	DESCRIPTION	DATE	DWN	APVD
1	INITIAL PROPOSAL	25MAY2015	FL	FY



SECTION W-W
(KEY POSITION)

Ø0.40 REF FINISHED HOLE
SEE APPLICATION SPEC
⊕ 0,05 X Z



PIN LAYOUT

ROW	h	1	1	4	2	2	4	2	2	4	2	2	4	2	2	4
ROW g	4	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4
ROW f	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4	2
ROW e	4	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4
ROW d	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4	2
ROW c	4	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4
ROW b	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4	2
ROW a	4	2	2	4	2	2	4	2	2	4	2	2	4	2	2	4
COLUMN	1	2	3	4	5	6	7	8	9	10	11	12				

1 PIN LENGTH: 2.25mm
2 PIN LENGTH: 3.10mm
4 PIN LENGTH: 4.65mm

THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

BOARD THICKNESS 1,2 MIN

RECOMMENDED PCB LAYOUT
(COMPONENT SIDE SHOWN)

NOTES:
△ PLATING: 0,5µm MIN. TIN OVER NICKEL.
△ PLATING:

PARTNUMBER	PERFORMANCE LEVEL
2170919-1	PERFORMANCE LEVEL 1: CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III: UNCONTROLLED ENVIRONMENT APPLICATIONS. SEE PRODUCT SPEC 108-19353
2170919-2	PERFORMANCE LEVEL 2: CONFORMS TO ALL TESTING ACCORDING PRODUCT SPEC 108-19320, -250 MATING CYCLES, 4 DAYS MIXED GAS TEST PER IEC 60068-2-60 METHOD 1

3. CONSULT APPLICATION SPEC OR CONTACT TE CONNECTIVITY FOR PERMISSIBLE CONTACT ASSIGNMENTS.
△ CONNECTOR MARKED WITH PARTNUMBER AND DATE CODE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: FRED LIU 25MAY15	TE Connectivity
DIMENSIONS: mm		CHK: ALEX SHOAL 25MAY15	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: FRANK YANG 25MAY15	NAME: RIGHT ANGLE MALE CONNECTOR Z-PACK Slim UHD High Speed
0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.20 3 PLC ±0.025 4 PLC ±0.001 ANGLES ±0.001		SEE NOTE △	SIZE: 114-19106
MATERIAL: -		FINISH: -	WEIGHT: -
Customer Drawing		SCALE: 5:1	SHEET 1 OF 1 REV 1