

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC
APDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECN-23214009	23MAY2023	WLS	JS
	CI	REVISED PER ECN-24-266312	15MAY2024	WLS	JS

CAD
Pro-8DO NOT REVISE
EXCEPT BY CAD

19,9

7,3 MAX.

LOGO AND MANUFACTURING COUNTRY CODE

△ RAW MATERIAL ACC. TO SPEC. IEC 60335-1, GWEPT 750°C, WITHOUT FLAME.

6,0

2,8

5,5 MAX.

4,2 MAX.

	NATURAL	PA 6.6 UL94-V0 △	2-2133394-2
	NATURAL	PA6.6V0 OR PA6.6V0+PA6V0	2-2133394-1
OBSELETE	AMARELO/YELLOW	PA 6.6 UL94-V2	1-2133394-4
	VERMELHO/RED	PA 6.6 UL94-V2	1-2133394-3
	PRETO/BLACK	PA 6.6 UL94-V2	1-2133394-2
	NATURAL/NATURAL	PA 6.6 UL94-V2	1-2133394-1
	NATURAL/NATURAL	POLIPROPILENO/POLYPROPYLENE	2133394-2
	PRETO/BLACK	POLIPROPILENO/POLYPROPYLENE	2133394-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
H.C. CANTER | 17AUG2011CHK
W.L. STEFANI | 17AUG2011APVD
-

NAME

PRODUCT SPEC
-

HOUSING, .187 SERIES, FASTON REC.

APPLICATION SPEC
-

SIZE CAGE CODE DRAWING NO

RESTRICTED TO

WEIGHT
-

A3 00779 C-2133394

Customer Drawing

SCALE 4:1

SHEET 1 OF 1

REV CI

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0,5
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±1°

MATERIAL
-FINISH
-

1470-19 (3/11)