




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

| REVISIONS | | | | |
|-----------|-----|-------------------------------|-----------|-------|
| P | LTR | DESCRIPTION | DATE | APVD |
| A | | INITIAL REL. PER LC20-0118-17 | 18DEC2017 | JG BJ |
| B | | LC20-0031-18 / ECO-18-004486 | 04APR2018 | DM BJ |
| C | | LC20-0048-18 / ECO-18-006178 | 27APR2018 | DM BJ |
| CI | | LC20-0123-18 / ECO-18-018470 | 07DEC2018 | DM BJ |




- ACCOMMODATES:
 #2 AWG CPT-STD STR (Ø6.8-7.4 [.268-.292 DIA])
 #2 ACSR (Ø8.0 [.316 DIA])
 CONDUCTORS TO 2 HOLE NEMA PAD.
- MARKING:
 SEE TABLE
- HARDNESS: SOFT TEMPERED.
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- CONNECTOR CONTAINS FACTORY APPLIED ANTI-OXIDE INHIBITOR.
- RECOMMENDED PRESS TONNAGE:
 15 TON (12 TON MIN).
- INSTALLATION INSTRUCTION SHEET:
 408-32266.



| | | | | |
|--------------------|--|-------------|--------------|-----------|
| ELECTRO-TIN PLATED | STE KLD22NTN 2 STR CSA 24 [DATE CODE] | KLD22NTN | - | 2182738-2 |
| NONE | STE KLD22N 2 STR CSA 24 [DATE CODE] | KLD22N | 1059484 | 2182738-1 |
| FINISH | MARKING | CATALOG NO. | H.Q. SAP NO. | PART NO. |

SHOWN MARKING FOR 2182738-2



| QTY | DESCRIPTION | ITEM NO |
|-----|--------------|-----------------------------|
| 1 | CAP, PLASTIC | 3 |
| A/R | INHIBITOR | 2 |
| 1 | TIN PLATED | COMPRESSION LUG, ALUM ALLOY |
| - | UNPLATED | |
| -2 | -1 | |

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | | | |
|--------------------------|---|---|--|
| DIMENSIONS: mm [INCH] | TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH | DWN J. GUPPY 28SEP2017 CHK A. BULZA 15DEC2017 APVD B. JOHNSON 18DEC2017 | STE TE Connectivity |
| MATERIAL SEE BOM | SEE BOM | PRODUCT SPEC APPLICATION SPEC WEIGHT | NAME COMPRESSION TERMINAL, ALUMINUM, #2 STR, #2 ACSR CONDUCTOR TO 2 HOLE NEMA PAD |
| CUSTOMER DRAWING | | SIZE A2 CAGE CODE 00779 DRAWING NO. C-2182738 | RESTRICTED TO |

SCALE NTS SHEET OF REV CI