




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
K3		REVISED PER ECR-22-150475	26AUG2022	RK	MZ



	△4	.261	6-66460-2	202800-3	BLUE	213521-6
SUPERSEDED BY 213521-1	—	.261	66460-7	202800-3	BLUE	213521-5
	—	.659	66460-9	202800-4	BLACK	213521-4
	—	.470	66460-8	202800-4	BLACK	213521-3
	—	.261	66460-7	202800-4	BLACK	213521-2
	△2	.261	66460-7	202800-3	BLUE	213521-1

- 1 THIS ASSEMBLY MATES WITH 202799.
- △2 .000030 MIN GOLD PLATE ON .0625 DIA .250 FROM MATING END & REMAINDER GOLD FLASH ALL OVER .000050 MIN NICKEL. POSTS PLATED TIN-LEAD .000100 MIN THICK PER MIL-T-10727 OVER NICKEL .000050 MIN THK PER QQ-N-290.
- △3 JACKSCREW SOCKET: STAINLESS STEEL; PIN CONTACT: BRASS; RECEPTACLE BLOCK: BLUE = DIALLYL PHTHALATE; BLACK = PHENOLIC.
- △4 .000030 MIN GOLD PLATE ON .0625 DIA .250 FROM MATING END & REMAINDER GOLD FLASH ALL OVER .000050 MIN NICKEL. POSTS PLATED TIN .000100 MIN THICK PER MIL-T-10727 OVER NICKEL .000050 MIN THK PER QQ-N-290.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. ERDMAN 4-29-88	TE Connectivity	
DIMENSIONS: INCHES		CHK R. STONE 4-29-88	RECEPTACLE ASSEMBLY, 160 POSITION, POSTED, M SERIES	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APVD -	NAME	RESTRICTED TO
MATERIAL		PRODUCT SPEC	SIZE A2	CAGE CODE 00779
FINISH		APPLICATION SPEC	DRAWING NO C=213521	SCALE 2:1
		WEIGHT	SHEET 1 of 1	REV K3
		CUSTOMER DRAWING		