




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	INITIAL REL. PER LC20-0120-17	18DEC2017	JG BJ



- ACCOMMODATES: 477 STANDARD STRANDED (Ø20.12 [.792 DIA]) CONDUCTORS.
- MARKING: SEE TABLE
- HARDNESS: SOFT TEMPERED.
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- CONNECTOR CONTAINS FACTORY APPLIED ANTI-OXIDE INHIBITOR.
- RECOMMENDED PRESS TONNAGE: 15 TON.



ELECTRO-TIN PLATED	STE KSD047STN 477 STR CSA 30 [DATE CODE]	KSD047STN	2182750-2
NONE	STE KSD047S 477 STR CSA 30 [DATE CODE]	KSD047S	2182750-1
FINISH	MARKING	CATALOG NO.	PART NO.

QTY	DESCRIPTION	ITEM NO
1	CAP, PLASTIC	3
A/R	A/R INHBITOR	2
1	TIN PLATED	COMPRESSION SLEEVE, ALUM
-	UNPLATED	
-2	-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	J. GUPPY	22SEP2017
CHK	A. BULZA	15DEC2017
APVD	B. JOHNSON	18DEC2017

STE TE Connectivity

NAME: ALUMINUM COMPRESSION SPLICE, 477 KCMIL CONDUCTORS

SIZE: A2 | CAGE CODE: 00779 | DRAWING NO: C-2182750 | RESTRICTED TO: -

MATERIAL: SEE BOM | TOLERANCES UNLESS OTHERWISE SPECIFIED: SEE BOM | FINISH: SEE BOM

CUSTOMER DRAWING | SCALE: NTS | SHEET: 1 OF 1 | REV: A