






REVISIONS				
P	LTR	DESCRIPTION	DATE	APPD
D1		REVISED PER ECO-20-015561	09DEC2020	AP HC

**P1**

**P2**



- ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, EEPROM PROGRAM AND SIGNAL INTEGRITY.
- ROHS AND REACH COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE SPECIFICATION TEC-138-702.

△ LABEL INFORMATION:

2202507-[ ]	TE LOGO AND P/N
--- METERS	LENGTH
YYWW	DATE CODE
MADE IN ---	COUNTRY OF ORIGIN

△ LABEL INFORMATION:

2202507-[ ]	TE LOGO AND P/N
MINI-SAS HD	
YYWWSSSS	YYWW= DATE CODE, SSSS= SERIAL NUMBER
[Barcode]	BARCODE

- MINI-SAS HD EEPROM PROGRAMMED PER 2202507\_EEPROM.
- 1 ONLY: LABEL IS APPLIED TO THE CENTER OF CABLE ASSEMBLY.

	7	+0.1 -0	METERS	2202507-8
	6	+0.1 -0	METERS	2202507-7
	5	+0.1 -0	METERS	2202507-6
OBSOLETE	4	+0.08 -0	METERS	<del>2202507-5</del>
	3	+0.08 -0	METERS	2202507-4
OBSOLETE	2	+0.08 -0	METERS	<del>2202507-3</del>
	1	+0.08 -0	METERS	2202507-2
	0.5	+0.05 -0	METERS	2202507-1 △
	L			PART NO


THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC ±	1 PLC ±	2 PLC ±	3 PLC ±	4 PLC ±	ANGLES ±
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
			A1	00779	2202507		

CUSTOMER DRAWING SCALE 1:1 SHEET 1 OF 2 REV D1

TE Connectivity Ltd. CABLE ASSEMBLY, 26 AWG TURBOTWIN, MINI-SAS HD, 4X TO MINI-SAS, 4X

REVISIONS				
P	LTR	DESCRIPTION	DATE	APPD
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	DATE	09MAR2012
mm	0 PLC ± -	P.L.I.	DATE	09MAR2012
	1 PLC ± -	J.MEYERS	NAME	J.MEYERS
	2 PLC ± -	J.MEYERS	PRODUCT SPEC	APPLICATION SPEC
	3 PLC ± -		APPLIC. SPEC	
	4 PLC ± -		SIZE	A1
	ANGLES ± -		WEIGHT	0
MATERIAL	FINISH		SIZE	A1
			WEIGHT	0
			SIZE	A1
			WEIGHT	0
			SIZE	A1
			WEIGHT	0

TE Connectivity Ltd.

CABLE ASSEMBLY, 26 AWG TURBOTWIN, MINI-SAS HD, 4X TO MINI-SAS, 4X

00779 ©=2202507

CUSTOMER DRAWING

SCALE 1:1 SHEET 2 OF 2 REV D1