





P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER ECR-25-241820	18APR2025	GC	JM




NOTES:

- ① MATERIAL CONTACTS; PHOSPHORBRONZE
- ② MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
- ③ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND COMPLIANT PIN SECTION: 0,5µm TIN-LEAD MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- ④ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
- ⑤ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
- ⑥ ASSEMBLY PRINTED WITH P/N AND DATECODE THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
- ⑦ POLE PATTERN FOR FEMALE CONNECTOR TYPE B-19 COLUMNS 95 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- ⑧ ROW "f" PLATED THROUGH HOLES FOR UPPERSHIELD
- ⑨ CONNECTOR & SHIELD LUBRICATED WITH BELLCORE PROVED LUBRICANT, TECHNICAL REFERENCE TR-NWT-001217 ISSUE 1, SEPT. 1992.
- CONNECTOR TESTED AND QUALIFIED AGAINST BELLCORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS
- ⑩ SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED ADHESIVE TAPE OR ADHESIVE.
- 10 BASIC P.N. LOWERSHIELD: 352029 OR 5352029



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



P.C.B. HOLE DIM. COMPLIANT PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		FINISH	MATERIAL	PARTNUMBER
DIN	25NOV2013	SANDERS YAN	—	2170864-1
CHK	—	FRANK YANG	—	TE Connectivity
APVD	25NOV2013	PRODUCT SPEC	NAME	Z-PACK 2mm HM
		108-19082		TYPE B - 19 COLUMNS
		APPLICATION SPEC		PRE-SHIELDED RECEPTACLE
		114-19029		
MATERIAL	FINISH	WEIGHT	RESTRICTED TO	
—	—	0.000000	A2	00779 C-2170864
			SCALE	5:1
			HEET	1 OF 1
			REV	C