

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL REL PER LC20-0092-20	07OCT2020	JG	BJ




FIGURE 1
(WITH cULus LOGO)

1. COPPER PLATING THICKNESS:
13 mil (330 microns) MIN.
2. cULus LISTING FOR 10' RODS.
3. UL LISTING FOR 8' RODS.
4. ALL DIMENSIONS ARE FOR REFERENCE ONLY.




FIGURE 2
(WITH UL LOGO)

1	6	12.70 (5.76)	10 (3050)	.125 (3.2)	.250 (6.4)	.681 (17.3)	3/4	CGR3410U13	EN3751-244
2	8	10.16 (4.61)	8 (2440)	.125 (3.2)	.250 (6.4)	.681 (17.3)	3/4	CGR3408U13	EN3751-243
3		7.63 (3.46)	6 (1830)	.125 (3.2)	.250 (6.4)	.681 (17.3)	3/4	CGR3406U13	-
		6.37 (2.89)	5 (1525)	.125 (3.2)	.250 (6.4)	.681 (17.3)	3/4	CGR3405U13	-
		5.09 (2.31)	4 (1220)	.125 (3.2)	.250 (6.4)	.681 (17.3)	3/4	CGR3404U13	-
1	6	8.73 (3.96)	10 (3050)	.125 (3.2)	.188 (4.8)	.559 (14.2)	5/8	CGR5810U13	EN3751-242
2	8	6.99 (3.17)	8 (2440)	.125 (3.2)	.188 (4.8)	.559 (14.2)	5/8	CGR5808U13	EN3751-241
3		5.25 (2.38)	6 (1830)	.125 (3.2)	.188 (4.8)	.559 (14.2)	5/8	CGR5806U13	-
		4.37 (1.98)	5 (1525)	.125 (3.2)	.188 (4.8)	.559 (14.2)	5/8	CGR5805U13	-
		3.50 (1.59)	4 (1220)	.125 (3.2)	.188 (4.8)	.559 (14.2)	5/8	CGR5804U13	-
1	6	7.01 (3.18)	10 (3050)	.094 (2.4)	.188 (4.8)	.500 (12.7)	1/2	CGR1210U13	-
2	8	5.62 (2.55)	8 (2440)	.094 (2.4)	.188 (4.8)	.500 (12.7)	1/2	CGR1208U13	-
3		4.21 (1.91)	6 (1830)	.094 (2.4)	.188 (4.8)	.500 (12.7)	1/2	CGR1206U13	-
		3.50 (1.59)	5 (1525)	.094 (2.4)	.188 (4.8)	.500 (12.7)	1/2	CGR1205U13	EN3751-240
		2.82 (1.28)	4 (1220)	.094 (2.4)	.188 (4.8)	.500 (12.7)	1/2	CGR1204U13	-
FIGURE		WEIGHT lbs (kg)	L FEET (mm)	B	A	ØD	NOMINAL DIAMETER	CATALOG NO.	PART NO.




FIGURE 3
(WITHOUT UL LOGO)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. GUPPY 09SEP2020	TE Connectivity			
DIMENSIONS: INCHES (mm)		CHK J. OPEL 28SEP2020				
		APVD B. JOHNSON 05OCT2020	NAME GROUND ROD, UNTHREADED COPPER COATED 13 mil (330 microns)			
		PRODUCT SPEC				
MATERIAL STEEL CORE		APPLICATION SPEC				
		WEIGHT				
		CUSTOMER DRAWING				
		SCALE NTS	SHEET 1	OF 1	REV B	RESTRICTED TO -