







REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
B2		REVISED PER ECN-22-137994	05MAY2022	KB BT
B3		REVISED PER ECN-22-155818	25MAY2022	KB BT
B4		REV PER ECN-24-265072	21MAY2024	JMS BDK
B5		REV PER ECN-24-279703	20AUG2024	SMR BK



1. COIL ECONOMIZATION IS NOT REQUIRED BUT CAN BE USED TO REDUCE OVERALL POWER AND TEMPERATURE RECOMMENDED MINIMUM HOLD CURRENT AFTER PULL-IN IS 250ma FOR PROPER FUNCTION.
2. SPST-NO-DM (1 FORM X).
3. MEASURED AT DATUM TARGETS X1 THROUGH X4.
4. MEASURED AT DATUM TARGETS Y1 THROUGH Y4.
5. LOAD TERMINALS (HAS POLARITY). SUITABLE CRIMP TERMINAL, USE TE MCP 9.5, P/N 1-967589-2, WITH 6AWG WIRE FOR 80A.
6. COIL TERMINALS (NO POLARITY). SUITABLE CRIMP TERMINAL USE TE P/N 6-160526-1.
7. OCR CODE TO APPEAR IN THIS AREA:YYJJJHHMMSS
YY-LAST TWO DIGITS OF THE YEAR, JJJ-JULIAN DAY OF THE YEAR, HH-HOUR, MM-MINUTE, SS-SECOND



SUPERSEDED BY	2203997-3
2390660-1	2203997-2
	2203997-1
	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: R. VESTAL 12AUG2014	TE Connectivity	
DIMENSIONS: mm		CHK: T. BLACKMON 12AUG2014	NAME: ASSEMBLY, EVC80	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: T. BLACKMON 12AUG2014	SIZE: A 00779 C=2203997	
0 PLC	±	PRODUCT SPEC	RESTRICTED TO	
2 PLC	±0.3	APPLICATION SPEC	SCALE: 2:1 SHEET 1 OF 1 REV: B5	
3 PLC	±0.10	WEIGHT		
4 PLC	±	CUSTOMER DRAWING		
ANGLES	±1°			
FINISH				