



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.





LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A	ECR-15-013671	17SEP2015	B.L	H.W		



2199296-1; ASSY SHOWN

MATERIAL:
 CONTACT: COPPER ALLOY
 HOUSING: UL 94V-0, THERMOPLASTIC, COLOR: BLACK
 SHELL: STAINLESS STEEL

FINISH:
 CONTACT: GOLD PLATING ON CONTACT SURFACE AND SOLDER TINE SURFACE
 ALL OVER NICKEL UNDER PLATING
 SHELL: ALL OVER TIN PLATING
 ALL OVER NICKEL UNDER PLATING
 COMPLANARITY 0.10 MAX.
 PICK UP AND PLACE AREA
 COPPER FOIL THICKNESS: 10Z . (0.035MM)
 TRACE WIDTH FOR PIN 1 AND 5: 1.0MM




RECOMMENDED PWB LAYOUT VIEWED FROM CONNECTOR MOUNT SIDE
 GENERAL TOLERANCE: ±0.05


OBSCOLETE

PIN DEFINITION

PIN NO.	CASE 1	CASE 2
PIN 13	CONTROL-4	TBD
PIN 12	CONTROL-3	AUX, HPD
PIN 11	CONTROL-2	Main Link, LD-
PIN 10	CONTROL-1	Main Link, LD+
PIN 9	StdA_SSTX+	StdA_SSTX+
PIN 8	StdA_SSTX-	StdA_SSTX-
PIN 7	StdA_SSRX+	StdA_SSRX+
PIN 6	StdA_SSRX-	StdA_SSRX-
PIN 5	GND-uUSB	GND-uUSB
PIN 4	ID	ID
PIN 3	D+	D+
PIN 2	D-	D-
PIN 1	VBUS	VBUS



BOTTOM VIEW WITHOUT SHELL





THIS DRAWING IS A CONTROLLED DOCUMENT.




DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	9 JUNE 2013
mm	0 PLC ±	CHK	BILL LV
	1 PLC ±0.15	CHK	XU XIANG
	2 PLC ±0.15	APVD	9 AUG 2012
	3 PLC ±0.15	APVD	MARK WESTEN
	4 PLC ±0.15	PRODUCT SPEC	108-115055
	ANGLES ±3°	APPLICATION SPEC	
MATERIAL	FINISH	WEIGHT	NAME
1	2		MULTI I/O 5+4+4
			STD, ON BOARD
			RECEPTACLE ASSEMBLY FLANGE TYPE
		Customer Drawing	SIZE
			A2
			CAGE CODE
			00779
			DRAWING NO
			C-2199296
			RESTRICTED TO
			SCALE
			10:1
			SHEET
			1
			OF
			2
			REV
			A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1			




NOTES:
OTHER ITEMS AND DIMENSION, PLEASE REFER TO SHEET 1



OBESOLETE


PIN DEFINITION

PIN 9	StdA_SSTX+
PIN 8	StdA_SSTX-
PIN 7	StdA_SSRX+
PIN 6	StdA_SSRX-
PIN 5	GND-uUSB
PIN 4	ID
PIN 3	D+
PIN 2	D-
PIN 1	VBUS
PIN NO.	SIGNAL NAME



BOTTOM VIEW WITHOUT SHELL

RECOMMENDED PWB LAYOUT
VIEWED FROM CONNECTOR MOUNT SIDE
GENERAL TOLERANCE: ±0.05



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	9 JUNE 2013	 TE Connectivity
mm	0 PLC ±	CHK	BILL LV	
	1 PLC ±0.15	APVD	XU XIANG	
	2 PLC ±0.15	APVD	MARK WESTEN	
	3 PLC ±0.15	PRODUCT SPEC	108-115055	NAME
	4 PLC ±0.15	APPLICATION SPEC		MULTI I/O 5+4+4
MATERIAL	ANGLES ±3°	FINISH		STD, ON BOARD
				RECEPTACLE ASSEMBLY FLANGE TYPE
		WEIGHT		SIZE
				CAGE CODE
				DRAWING NO
				RESTRICTED TO
				A200779
				C-2199296
				SCALE
				10:1
				SHEET
				2
				OF
				2
				REV
				A

Customer Drawing