










THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
A		NEW DRAWING	22JUN2012	MT	HR		
A1		DRAWING UPDATE	22MAY2013	MT	HR		
B		E-14-015968	27OCT2014	JR	JR		
B1		E-14-017561	24NOV2014	-	-		



CODINGS



- NOTES**
- 1 USED ON INTERFACE: PN. 114-94190
 - 2 PACKAGING: LOOSE PIECE
 - 3 WARPAGE MAX. ± 3.5mm PERMITTED
 - 4 FEMALE HOUSING MUST BE USED SEE TE C- DRAWING 2208304

SHOWN CODE A

TE- NO	REV.	CODE	COLOR	WEIGHT [g]	REGRIND	MATERIAL	DESCRIPTION
2208306-4		B	D	YELLOW	1.6	Max. 25% PBT-GF10	COVER, MQS. 8WAY
2208306-3		B	C	YELLOW	1.6	Max. 25% PBT-GF10	COVER, MQS. 8WAY
2208306-2		B	B	YELLOW	1.6	Max. 25% PBT-GF10	COVER, MQS. 8WAY
2208306-1		B	A	YELLOW	1.6	Max. 25% PBT-GF10	COVER, MQS. 8WAY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN M. TRAJKOV 22JUN2012	CHK H. RIPPER 22JUN2012	APVD -	NAME
0 PLC ±0.3	1 PLC ±0.3	PRODUCT SPEC	108-18030	APPLICATION SPEC	114-18021
2 PLC ±	3 PLC ±	WEIGHT	SEE TABLE A2	SIZE	00779
4 PLC ±	ANGLES ±°	CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV B1

STE TE Connectivity

COVER FOR 8WAY FEMALE HOUSING MQS. / SHORTING BAR