




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A4	ECR-21-103323	18MAY2021	NT JDB



VIEW A

NOTES:

- 1 PACKAGING: ACC. TO TE SPEC. 107-18064
- 2 ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.
SHORT-CIRCUIT AND CONTINUITY TEST AT 500V DC, 0.1s
- 3 WIRING SCHEMA ACC. TO TIA/EIA-568-B AS SHOWN IN WIRING SCHEDULE
- 4 PROP 65 WARNING LABEL: SEE SHEET 2
- 5 LABEL TEXT:
TE CONNECTIVITY
WW/YY/PRODUCTION LOCATION CODE

WIRING SCHEDULE 3

CAVITY SIDE A	COLOR
1	WH/OG
2	OG
3	WH/GN
4	BU
5	WH/BU
6	GN
7	WH/BN
8	BN

4	10000 (±300)	HiFlex MultiPurpose 70°C PUR	2-2205129-6
	5000 (±150)	HiFlex MultiPurpose 70°C PUR	2-2205129-5
	3000 (±50)	HiFlex MultiPurpose 70°C PUR	2-2205129-4
	2000 (±25)	HiFlex MultiPurpose 70°C PUR	2-2205129-3
	1000 (±15)	HiFlex MultiPurpose 70°C PUR	2-2205129-2
	500 (±10)	HiFlex MultiPurpose 70°C PUR	2-2205129-1
OBSOLETE	10000 (±300)	HI 125°C TPE	1-2205129-6
	5000 (±150)	HI 125°C TPE	1-2205129-5
	3000 (±50)	HI 125°C TPE	1-2205129-4
	2000 (±25)	HI 125°C TPE	1-2205129-3
	1000 (±15)	HI 125°C TPE	1-2205129-2
	500 (±10)	HI 125°C TPE	1-2205129-1
	10000 (±300)	STD 110°C PVC	2205129-6
	5000 (±150)	STD 110°C PVC	2205129-5
	3000 (±50)	STD 110°C PVC	2205129-4
	2000 (±25)	STD 110°C PVC	2205129-3
1000 (±15)	STD 110°C PVC	2205129-2	
500 (±10)	STD 110°C PVC	2205129-1	
	Length "L"	Cable version	TE PN


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2015 SATHISH KUMAR .G	TE Connectivity	
		CHK 03FEB2015 B.VELDHOVEN		
		APVD 03FEB2015 A.VAN ZANDVOORT	NAME	
		PRODUCT SPEC 108-78955	CA MINI IO TYPE I PIGTAIL	
		APPLICATION SPEC 114-5506		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
		0 PLC ± -		
		1 PLC ± -		
		2 PLC ± -		
		3 PLC ± -		
		4 PLC ± -		
		ANGLES ± 1°		
MATERIAL		FINISH		
		WEIGHT		
		A3 00779 C-2205129		
CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 2	REV A4

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

NOTES: CONTINUATION FROM SHEET 1:

- 4 PROP 65 WARNING LABEL:
- THE WARNING LABEL ON THE PRODUCT OR LOWEST LEVEL PACKAGING
 - CHEMICAL NAME: ANTIMONY TRIOXIDE



WARNING: This product can expose you to chemicals including ANTIMONY TRIOXIDE which is known to the state of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2015 SATHISH KUMAR .G	 TE Connectivity		
		CHK 03FEB2015 B.VELDHOVEN			
DIMENSIONS: mm 		APVD 03FEB2015 A.VAN ZANDVOORT	NAME CA MINI IO TYPE I PIGTAIL		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC 108-78955	RESTRICTED TO -		
MATERIAL -		APPLICATION SPEC 114-5506	SIZE A3	CAGE CODE 00779	DRAWING NO C-2205129
FINISH -		WEIGHT 0.000000	SCALE NTS		
CUSTOMER DRAWING			SHEET 2 OF 2		REV A4