


CABLE OUTLET POSITION 3

1:2





THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONAL IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZÜGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (Z.B. BIEGESCHLAFTES KABEL) KÖNNEN DIE DELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITÄT NICHT BEEINTRÄCHTIGT IST.

REVISIONS				
REV.	LTN	DESCRIPTION	DATE	APPROV.
F		BOM REVISIONS AND NOTES UPDATED.	15JUN2016	DS JJ
G		COMPONENTS CHANGED, NOTES UPDATED	05DEC2016	JM JJ
H		COMPONENT (CABLE, 2 x 0.75 mm ²) REVISED	27NOV2018	JM JJ
J		ITEM NO. 5 (INSULATION COVER) REVISED	01OCT2020	JM JJ

INTERFACE VIEW
Schnittstellen Ansicht



LENGTH SCHEDULE:
Laengentabelle:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	CABLE OUTLET POSITION
2-2208882-1	J	1000	+30	Position 3
2-2208882-5	J	5000	+60	

NOTES

- PACKAGING ACCORDING SPECIFICATION V2208882.
- STRIPPED ONLY OUTER JACKET, BRAID AND FOIL. ELECTRICAL TESTING IS ACCORDING APPLICATION SPECIFICATION.
- APPLICATION SPECIFICATION: 114-94212 CHARGE INLETGB/T20234.2.
- CUTTING LENGTHS TO BE FIXED BY MANUFACTURING.
- MANUFACTURING CODE: TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY), TO BE PRINTED ON LABEL (ITEM 15). LABEL TO BE APPLIED TO THE CABLE AFTER SUCCESSFUL ELECTRICAL TEST.

WIRING SCHEDULE:

Belegungsplan:

CAVITY-NO.	IDENTIFICATION	WIRE COLOUR	WIRE SECTION
1	L	RED	4mm ² (ITEM 12)
2	N	BROWN	4mm ² (ITEM 12)
3	GROUND/EARTH	BROWN	4mm ² (ITEM 13)
4	CP	BROWN/WHITE	0.75mm ² (ITEM 14)
5	CC	WHITE	0.75mm ² (ITEM 14)

LABEL LEGEND:

Label Beschriftung:



TE PART NO., CURRENT REVISION
TE Teilenummer, aktuelle Revision

PRODUCTION DATE
Produktionsdatum

3	CAB TIE, CLIP, HELL, T18R-HR-N46	16
1	LABEL, HELL	15
SPP table	CABLE, 2 x 0.75 mm ² , BLACK	14
SPP table	CABLE, 4 mm ² , BROWN	13
SPP table	CABLE 2 x 4.0 mm ² , BRAID	12
2	SEALING	11
3	SEALING	10
2	DIA 3MM CON. CONTACT	9
3	DIA 6MM CON. CONTACT	8
4	SELF TAPPING SCREW	7
2	FAMILY SEAL, MIXED, Vers.1	6
1	INSULATION COVER, TE, COVER INLET	5
1	CABLE FIXATION, TE, COVER INLET	4
1	ACTUATOR, LOCKING UNIT, ASSY	3
1	2. LOCK, TE, INLET GB	2
1	5 POS. MIXED, HSG, INLET GB	1
QTY X-Y	DESCRIPTION	ITEM NO.
-	WEIGHT OF ASSY NO. (g)	-

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
0 PLC	±	0.10	±
1 PLC	±	0.15	±
2 PLC	±	0.20	±
3 PLC	±	0.30	±
4 PLC	±	0.40	±
ANGLES	±	0.10	±
		FINISH	

PRODUCT CHARACTERISTICS ACC. QMP EMEA_12		TOLERANCING ISO 8015	
BESONDERE MERKMALE NACH QMP EMEA_12		TOLERIERUNG ISO 8015	
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DNW	03JUL2013
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)		M. Zelch	03JUL2013
		J. Bernstorff	
		M. folk	04JUL2013
		APPROV	
		PRODUCT SPEC	
		APPLICATION SPEC	
		see note 3	
		WEIGHT	
		CUSTOMER DRAWING	

2- X AS SHOWN
wie dargestellt



NAME		RESTRICTED TO	
HV, CHARGE INLET TYPE GB, HYB ASSY, 4 sqmm			
SIZE	CAGE CODE	DRAWING NO	
A	00779	©=2208882	
SCALE	1:1	SHEET	1 OF 1
REV	J		