










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	New drawing created.	23JUL2013	Kirs. Mair.	
	A1	NOTE 7 IS ADDED	22AUG2017	GH	RM



- 1 TO BE USED ON TAB 1.5+/-0.1 x 0.8+0.04/-0.03
Geeignet fuer Flachstecker 1.5+/-0.1 x 0.8+0.04/-0.03
- 2 MAXIMUM INSERTION DEPTH
Groesste Einstecktiefe
- 3 LASERWELDED
Lasergeschweisst
- 4 BRANDNAME AND REVISION STATUS
Hersteller-Logo und Revisionsstand
- 5 1µm TO 1.4 µm GOLDPLAE OVER NICKEL IN CONTACT AREA;
TIN PLATED REMAINDER.
1µm bis 1.4 µm Goldueberzug ueber Nickel im Kontaktbereich;
Rest galvanisch verzinkt.
- 6 INDEX AT SPRING FOR GOLDPLATING
Kennzeichnung an der Ueberfeder fuer Vergoldung
- A1 7 INDEX "Au" FOR GOLDPLATING
Kennzeichnung "Au" nur fuer Goldoberflaeche

5	CuNiSi	2236700-1	A
FINISH	MATERIAL	PART NO	REV



SINGLE WIRE SEAL
Einzeldichtung

SINGLE WIRE SEAL Einzeldichtung			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23JUL2013 CHK 24JUL2013 APVD 24JUL2013		NAME	
184140-1	1.6 - 2.1	ORANGE orange	DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0-PLC 1-PLC 2-PLC 3-PLC 4-PLC ANGLES FINISH	±0.1 ±0.1 ±0.1 ±0.1 ±0.1 ±0.1 ±0.1	108-18617-0 APPLICATION SPEC	116-18254-0 WEIGHT
184139-1	1.2 - 1.7	BLUE blau	MATERIAL	-	-	-	108-18617-0 APPLICATION SPEC	116-18254-0 WEIGHT
ORDER NO. Bestell-Nr.	INSULATION DIA Isolations Ø	COLOUR Farbe	Customer Drawing		SCALE 10:1		SHEET 1 OF 1	
							REV A1	