


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	REVISED PER ECR-18-014190	11SEP2018	BDA KR



1 CONTINUOUS STRIP ON REELS AT 5.08±0.08 [.200±.003] CENTERS.  
 2 SLOTTED ACCEPTS A SINGLE OR DOUBLE WIRE OF SAME SIZE AND TYPE.  
 COPPER MAGNET WIRE:  
 DIA 0.18-0.23mm [#33-#31] AWG  
 ALUMINUM MAGNET WIRE:  
 DIA 0.23-0.29mm [#31-#29] AWG



2238088-1  
 PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B WAYNE 25FEB2015	<b>STE</b> TE Connectivity	
DIMENSIONS: MM [INCHES]		CHK KURT RANDOLPH 25FEB15		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD KURT RANDOLPH 25FEB15	NAME TAB, FASTON, .110 SERIES 187 SERIES MAG-MATE	
0 PLC ± -		PRODUCT SPEC 108-2012	SIZE A3	
1 PLC ± -		APPLICATION SPEC 114-2069	CAGE CODE 00779	DRAWING NO C-2238088
2 PLC ± 0.25 [.010]		WEIGHT -	RESTRICTED TO -	
3 PLC ± -		MATERIAL BRASS	SCALE 8:1	
4 PLC ± -			SHEET 1 OF 1	
ANGLES ± -		FINISH TIN		REV A
MATERIAL BRASS		CUSTOMER DRAWING		