



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-23-204473	23MAR2023	PS	TD
	A1	NOTES AND TABLE UPDATED	15APR2024	PS	TD

1. CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.08±0.08 CENTERS.




2. SLOT TERMINATES EITHER A SINGLE OR TWO MAGNET WIRES OF THE SAME SIZE AND TYPE.  
COPPER MAGNET WIRE RANGE: #30-#27 AWG[0.25-0.36mm]  
ALUMINUM MAGNET WIRE RANGE: #28-#25 AWG[0.40-0.45mm]  
ALUMINUM WIRE CAN ONLY BE USED IN COMBINATION WITH POST-TIN PLATED TERMINAL PART NUMBERS.

3. POKE-IN ACCEPTS 2.92mm WIDTH X 0.50mm THICKNESS TAB.


4. CAVITY DESIGN REFER 1969944




IDENTIFICATION NUMBER 6 FOR MAGNET WIRE RANGE



DIRECTION FOR TOP OF REEL



TIN PLATED	BRASS	2238249-1
FINISH	MATERIAL	PART NUMBER
 TE Connectivity		
NAME: TERMINAL, POKE-IN, 200 SERIES MAG-MATE		
SIZE: A2	CAGE CODE: 00779	DRAWING NO: C-2238249
RESTRICTED TO: -	SCALE: 17:1	SHEET: 1 OF 1
REV: A1		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: B. WEAVER 11JUN2020
DIMENSIONS: mm		CHK: K. RANDOLPH 11JUN2020
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: W. MOYER 11JUN2020
0 PLC ±		PRODUCT SPEC
1 PLC ±		108-2012
2 PLC ±0.25		APPLICATION SPEC
3 PLC ±		114-160157
4 PLC ±		WEIGHT: -
ANGLES ±2°		CUSTOMER DRAWING
FINISH		SCALE: 17:1
SEE TABLE		SHEET: 1 OF 1
SEE TABLE		REV: A1