



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER ECN-24-247111	05FEB2024	RK	CAS



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 THE TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 PRELIMINARY PART NUMBER NOT RELEASED FOR PRODUCTION.
- 4 .000030 GOLD ON THE CONTACT AREA, MATTE TIN ON SOLDER AREA, ALL OVER .000050 NICKEL.
- 5 .000003 GOLD OVER .000027 Pd/Ni ON THE CONTACT AREA, MATTE TIN ON SOLDER AREA, ALL OVER .000050 NICKEL.
- 6 HOUSING: FLAME RETARDENT THERMOPLASTIC  
COLOR: BLACK  
POSTS: PHOS BRONZE




RECOMMENDED HOLE LAYOUT

FINISH	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	
OBSOLETE	4	3.984	3.900	39	80	4-2267065-0
3	4	3.884	3.800	38	78	3-2267065-9
3	4	3.784	3.700	37	76	3-2267065-8
3	4	3.684	3.600	36	74	3-2267065-7
3	4	3.584	3.500	35	72	3-2267065-6
3	4	3.484	3.400	34	70	3-2267065-5
3	4	3.384	3.300	33	68	3-2267065-4
3	4	3.284	3.200	32	66	3-2267065-3
3	4	3.184	3.100	31	64	3-2267065-2
3	4	3.084	3.000	30	62	3-2267065-1
OBSOLETE	4	2.984	2.900	29	60	3-2267065-0
3	4	2.884	2.800	28	58	2-2267065-9
3	4	2.784	2.700	27	56	2-2267065-8
3	4	2.684	2.600	26	54	2-2267065-7
OBSOLETE	4	2.584	2.500	25	52	2-2267065-6
OBSOLETE	4	2.484	2.400	24	50	2-2267065-5
3	4	2.384	2.300	23	48	2-2267065-4
OBSOLETE	4	2.284	2.200	22	46	2-2267065-3
3	4	2.184	2.100	21	44	2-2267065-2
3	4	2.084	2.000	20	42	2-2267065-1
OBSOLETE	4	1.984	1.900	19	40	2-2267065-0
OBSOLETE	4	1.884	1.800	18	38	1-2267065-9
3	4	1.784	1.700	17	36	1-2267065-8
OBSOLETE	4	1.684	1.600	16	34	1-2267065-7
3	4	1.584	1.500	15	32	1-2267065-6
OBSOLETE	4	1.484	1.400	14	30	1-2267065-5
3	4	1.384	1.300	13	28	1-2267065-4
OBSOLETE	4	1.284	1.200	12	26	1-2267065-3
OBSOLETE	4	1.184	1.100	11	24	1-2267065-2
OBSOLETE	4	1.084	1.000	10	22	1-2267065-1
OBSOLETE	4	.984	.900	9	20	1-2267065-0
OBSOLETE	4	.884	.800	8	18	2267065-9
OBSOLETE	4	.784	.700	7	16	2267065-8
OBSOLETE	4	.684	.600	6	14	2267065-7
OBSOLETE	4	.584	.500	5	12	2267065-6
OBSOLETE	4	.484	.400	4	10	2267065-5
OBSOLETE	4	.384	.300	3	8	2267065-4
OBSOLETE	4	.284	.200	2	6	2267065-3
OBSOLETE	4	.184	.100	1	4	2267065-2
OBSOLETE	4	.084	-	-	2	2267065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 03FEB2014	TE Connectivity Ltd.	
DIMENSIONS: INCHES		CHK MILLER MICHAEL 03FEB2014	ASSEMBLY, MOD II, HEADER, DR, .100 X .100 CL. VERTICAL, .025 SQUARE POSTS	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APVD MILLER MICHAEL 03FEB2014	RESTRICTED TO	
MATERIAL 6		FINISH 4	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		WEIGHT -	DRAWING NO C=2267065	SCALE -
		SHEET 1 of 2		REV A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

FINISH	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	
OBSOLETE	5	3.984	3.900	39	80	9-2267065-0
3	5	3.884	3.800	38	78	8-2267065-9
3	5	3.784	3.700	37	76	8-2267065-8
3	5	3.684	3.600	36	74	8-2267065-7
3	5	3.584	3.500	35	72	8-2267065-6
3	5	3.484	3.400	34	70	8-2267065-5
3	5	3.384	3.300	33	68	8-2267065-4
3	5	3.284	3.200	32	66	8-2267065-3
3	5	3.184	3.100	31	64	8-2267065-2
3	5	3.084	3.000	30	62	8-2267065-1
OBSOLETE	5	2.984	2.900	29	60	8-2267065-0
3	5	2.884	2.800	28	58	7-2267065-9
3	5	2.784	2.700	27	56	7-2267065-8
3	5	2.684	2.600	26	54	7-2267065-7
OBSOLETE	5	2.584	2.500	25	52	7-2267065-6
OBSOLETE	5	2.484	2.400	24	50	7-2267065-5
3	5	2.384	2.300	23	48	7-2267065-4
OBSOLETE	5	2.284	2.200	22	46	7-2267065-3
3	5	2.184	2.100	21	44	7-2267065-2
3	5	2.084	2.000	20	42	7-2267065-1
OBSOLETE	5	1.984	1.900	19	40	7-2267065-0
OBSOLETE	5	1.884	1.800	18	38	6-2267065-9
3	5	1.784	1.700	17	36	6-2267065-8
OBSOLETE	5	1.684	1.600	16	34	6-2267065-7
3	5	1.584	1.500	15	32	6-2267065-6
OBSOLETE	5	1.484	1.400	14	30	6-2267065-5
3	5	1.384	1.300	13	28	6-2267065-4
OBSOLETE	5	1.284	1.200	12	26	6-2267065-3
OBSOLETE	5	1.184	1.100	11	24	6-2267065-2
OBSOLETE	5	1.084	1.000	10	22	6-2267065-1
OBSOLETE	5	.984	.900	9	20	6-2267065-0
OBSOLETE	5	.884	.800	8	18	5-2267065-9
OBSOLETE	5	.784	.700	7	16	5-2267065-8
OBSOLETE	5	.684	.600	6	14	5-2267065-7
OBSOLETE	5	.584	.500	5	12	5-2267065-6
OBSOLETE	5	.484	.400	4	10	5-2267065-5
OBSOLETE	5	.384	.300	3	8	5-2267065-4
OBSOLETE	5	.284	.200	2	6	5-2267065-3
OBSOLETE	5	.184	.100	1	4	5-2267065-2
OBSOLETE	5	.084	-	-	2	5-2267065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2014 NAGALAKSHMI K	 TE Connectivity Ltd.	
DIMENSIONS: INCHES		CHK 03FEB2014 MILLER MICHAEL		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 03FEB2014 MILLER MICHAEL	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC	ASSEMBLY, MOD II, HEADER, DOUBLE ROW, .100 X .100 CL. VERTICAL, .025 SQUARE POSTS	
MATERIAL		APPLICATION SPEC	SIZE	RESTRICTED TO
FINISH		WEIGHT -	A2 00779	-
		CUSTOMER DRAWING	CAGE CODE	DRAWING NO
			00779	C-2267065
			SCALE	SHEET
			-	2 of 2
				REV A1