






REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
A		RELEASED ECO-20-007466	02JUN2020	DS DS



1. MATING PART: TE P/N 2203859.
2. USE CORRUGATE TUBING NW21
3. TPA SHOWN IN PRE-STAGED (AS SHIPPED) POSITION.
4. KEY MARKING IN APPROXIMATE AREA SHOWN.
5. ASSEMBLY P/N AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN. SEE TABLE FOR P/N TO KEY RELATIONSHIP.
6. SEE TABLE FOR CAP HOUSING COLOR TO KEY RELATIONSHIP.
7. USE MOUNTING CLIP, TE P/N 2203876. SEE TABLE ON SHEET 2 FOR RECOMMENDED PANEL THICKNESSES.




CIRCUITS	COLOR	DESCRIPTION	PART NO
24 POSITION (4) SIZE 12 (20) SIZE 20	GRAY	CAP ASSEMBLY, 24 POSITION, KEY F	2272889-6
	BROWN	CAP ASSEMBLY, 24 POSITION, KEY E	2272889-5
	BLACK	CAP ASSEMBLY, 24 POSITION, KEY D	2272889-4
16 POSITION (4) SIZE 12 (12) SIZE 16	GRAY	CAP ASSEMBLY, 16 POSITION, KEY C	2272889-3
	BROWN	CAP ASSEMBLY, 16 POSITION, KEY B	2272889-2
	BLACK	CAP ASSEMBLY, 16 POSITION, KEY A	2272889-1


PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: D STRAUSSER 12FEB2014	TE Connectivity
DIMENSIONS: mm		CHK: D STRAUSSER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: D STRAUSSER 02JUN2020	NAME: AMPSEAL ML CAP ASSEMBLY
0 PLC ±		PRODUCT SPEC: 108-151063	
1 PLC ±		APPLICATION SPEC: 114-151063	SIZE: A1 CAGE CODE: - DRAWING NO: C=2272889
2 PLC ±		WEIGHT: 79g	
3 PLC ±		CUSTOMER DRAWING	RESTRICTED TO: -
4 PLC ±			SCALE: 2:1 SHEET: 1 OF 3 REV: A
ANGLES ±			
FINISH			


REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



MOUNTING CLIP IN PRE-LATCHED POSITION





MOUNTING CLIP IN LATCHED POSITION




CAP ASSEMBLY WITH OPTIONAL WIRE SHIELD, PN 2203956

DIM A ± 0.10



SUGGESTED PANEL CUT-OUT



CAP ASSEMBLY WITH OPTIONAL WIRE SHIELD, PN 2203956
 90° ELBOW, PN 2272307


COLOR	DIM A PANEL THICKNESS	PART NO
BLACK	3.0 \pm 0.10	2203876-3
YELLOW	4.0 \pm 0.10	2203876-2
RED	5.0 \pm 0.10	2203876-1

MOUNTING CLIP INFORMATION

THIS DRAWING IS A CONTROLLED DOCUMENT.


DWN	D STRAUSSER	12FEB2014	TE Connectivity
CHK	D STRAUSSER	-	
APVD	D STRAUSSER	02JUN2020	
NAME	AMPSEAL ML CAP ASSEMBLY		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC
mm	0 PLC	\pm	108-151063
	1 PLC	\pm	APPLICATION SPEC
	2 PLC	\pm	114-151063
	3 PLC	\pm	WEIGHT
	4 PLC	\pm	79g
	ANGLES	\pm	CUSTOMER DRAWING
MATERIAL	FINISH		SCALE 2:1 SHEET 2 OF 3 REV A

REVISIONS				
P.	LTN	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-




9.50 9.50

2203866-1
16 POSITION
KEY A




13.50 13.50

2203866-2
16 POSITION
KEY B




17.50 17.50

2203866-3
16 POSITION
KEY C




13.50 9.50

2203866-4
24 POSITION
KEY D



17.50 13.50

2203866-5
24 POSITION
KEY E



9.50 17.50

2203866-6
24 POSITION
KEY F

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: D STRAUSSER 12FEB2014	
DIMENSIONS: mm		CHK: D STRAUSSER	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		APVD: D STRAUSSER 02JUN2020	NAME: AMPSEAL ML CAP ASSEMBLY
MATERIAL: -		PRODUCT SPEC: 108-151063	RESTRICTED TO: -
FINISH: -		APPLICATION SPEC: 114-151063	SIZE: A1
CUSTOMER DRAWING		WEIGHT: 79g	SCALE: 2:1
		CAGE CODE: -	SHEET 3 OF 3
		DRAWING NO: C=2272889	REV: A