


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	A	INITIAL ISSUE		30APR14	AW	JL	



NOTES :

- PART NUMBER 2246254-1 AS SHOWN.
- BRAIDS AND CONDUCTOR SHOULD BE TINNED.
- 100% OPEN/SHORT TEST.
- NORMAL IMPEDANCE 50 OHMS.
- VOLTAGE RATING 250 Vrms.
- DURABILITY 50 TIMES.
- TEMPERATURE RANGE -40 TO 90 DEGREE C.
- PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY STANDARD TEC-138-702.

1	PC	I-PEX CONN, U.FL MICRO	2
AR	MR	COAXIAL CABLE, OD 1.13MM	1
-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Allen Wang 30APR14	STE TE Connectivity														
DIMENSIONS: mm		CHK Victor Wang 30APR14															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Jason Lu 30APR14	NAME CABLE GPRS X07														
<table border="1"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC -	APPLICATION SPEC -		
0 PLC	± -																
1 PLC	± -																
2 PLC	± -																
3 PLC	± -																
4 PLC	± -																
ANGLES	± -																
MATERIAL -		FINISH -	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2246254	RESTRICTED TO -										
CUSTOMER DRAWING			SCALE -	SHEET 1 OF 1	REV A												