





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER ECN-24-247111	05FEB2024	RK	CAS



RECOMMENDED HOLE LAYOUT

- 1 TOLERANCE NON-CUMULATIVE.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 .000015 GOLD ON CONTACT AREA, MATTE TIN ON SOLDER AREA. ALL OVER .000050 NICKEL.
- 4 .000003 GOLD OVER .000012 Pd/Ni ON CONTACT AREA MATTE TIN ON SOLDER AREA. ALL OVER .000050 NICKEL.
- 5 HOUSING: FLAME RETARDANT THERMOPLASTIC
COLOR: BLACK
POST : PHOS. BRONZE
- 6 PRELIMINARY PART NUMBER NOT RELEASED FOR PRODUCTION.

OBSOLETE	3	3.984	3.900	39	40	4-2267064-0
6	3	3.884	3.800	38	39	3-2267064-9
6	3	3.784	3.700	37	38	3-2267064-8
6	3	3.684	3.600	36	37	3-2267064-7
6	3	3.584	3.500	35	36	3-2267064-6
6	3	3.484	3.400	34	35	3-2267064-5
6	3	3.384	3.300	33	34	3-2267064-4
6	3	3.284	3.200	32	33	3-2267064-3
6	3	3.184	3.100	31	32	3-2267064-2
6	3	3.084	3.000	30	31	3-2267064-1
6	3	2.984	2.900	29	30	3-2267064-0
6	3	2.884	2.800	28	29	2-2267064-9
6	3	2.784	2.700	27	28	2-2267064-8
6	3	2.684	2.600	26	27	2-2267064-7
OBSOLETE	3	2.584	2.500	25	26	2-2267064-6
6	3	2.484	2.400	24	25	2-2267064-5
6	3	2.384	2.300	23	24	2-2267064-4
6	3	2.284	2.200	22	23	2-2267064-3
6	3	2.184	2.100	21	22	2-2267064-2
6	3	2.084	2.000	20	21	2-2267064-1
OBSOLETE	3	1.984	1.900	19	20	2-2267064-0
6	3	1.884	1.800	18	19	1-2267064-9
6	3	1.784	1.700	17	18	1-2267064-8
6	3	1.684	1.600	16	17	1-2267064-7
6	3	1.584	1.500	15	16	1-2267064-6
OBSOLETE	3	1.484	1.400	14	15	1-2267064-5
6	3	1.384	1.300	13	14	1-2267064-4
6	3	1.284	1.200	12	13	1-2267064-3
OBSOLETE	3	1.184	1.100	11	12	1-2267064-2
OBSOLETE	3	1.084	1.000	10	11	1-2267064-1
OBSOLETE	3	.984	.900	9	10	1-2267064-0
6	3	.884	.800	8	9	2267064-9
OBSOLETE	3	.784	.700	7	8	2267064-8
6	3	.684	.600	6	7	2267064-7
OBSOLETE	3	.584	.500	5	6	2267064-6
OBSOLETE	3	.484	.400	4	5	2267064-5
OBSOLETE	3	.384	.300	3	4	2267064-4
OBSOLETE	3	.284	.200	2	3	2267064-3
OBSOLETE	3	.184	.100	1	2	2267064-2
OBSOLETE	3	.084	-	-	1	2267064-1

FINISH	C	B	A	NO OF POS	PART NO
--------	---	---	---	-----------	---------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	03FEB2014	NAGALAKSHMI K
CHK	03FEB2014	MILLER MICHAEL
APVD	03FEB2014	MILLER MICHAEL

TE Connectivity Ltd.

NAME: NAGALAKSHMI K
 PRODUCT SPEC: MILLER MICHAEL
 APPLICATION SPEC: MILLER MICHAEL

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=2267064 RESTRICTED TO: -

SCALE: 4:1 SHEET: 1 OF 2 REV: A1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

OBSOLETE	$\frac{4}{6}$	3.984	3.900	39	40	9-2267064-0
	$\frac{4}{6}$	3.884	3.800	38	39	8-2267064-9
	$\frac{4}{6}$	3.784	3.700	37	38	8-2267064-8
	$\frac{4}{6}$	3.684	3.600	36	37	8-2267064-7
	$\frac{4}{6}$	3.584	3.500	35	36	8-2267064-6
	$\frac{4}{6}$	3.484	3.400	34	35	8-2267064-5
	$\frac{4}{6}$	3.384	3.300	33	34	8-2267064-4
	$\frac{4}{6}$	3.284	3.200	32	33	8-2267064-3
	$\frac{4}{6}$	3.184	3.100	31	32	8-2267064-2
	$\frac{4}{6}$	3.084	3.000	30	31	8-2267064-1
	$\frac{4}{6}$	2.984	2.900	29	30	8-2267064-0
	$\frac{4}{6}$	2.884	2.800	28	29	7-2267064-9
	$\frac{4}{6}$	2.784	2.700	27	28	7-2267064-8
	$\frac{4}{6}$	2.684	2.600	26	27	7-2267064-7
OBSOLETE	$\frac{4}{6}$	2.584	2.500	25	26	7-2267064-6
	$\frac{4}{6}$	2.484	2.400	24	25	7-2267064-5
	$\frac{4}{6}$	2.384	2.300	23	24	7-2267064-4
	$\frac{4}{6}$	2.284	2.200	22	23	7-2267064-3
	$\frac{4}{6}$	2.184	2.100	21	22	7-2267064-2
	$\frac{4}{6}$	2.084	2.000	20	21	7-2267064-1
OBSOLETE	$\frac{4}{6}$	1.984	1.900	19	20	7-2267064-0
	$\frac{4}{6}$	1.884	1.800	18	19	6-2267064-9
	$\frac{4}{6}$	1.784	1.700	17	18	6-2267064-8
	$\frac{4}{6}$	1.684	1.600	16	17	6-2267064-7
	$\frac{4}{6}$	1.584	1.500	15	16	6-2267064-6
OBSOLETE	$\frac{4}{6}$	1.484	1.400	14	15	6-2267064-5
	$\frac{4}{6}$	1.384	1.300	13	14	6-2267064-4
	$\frac{4}{6}$	1.284	1.200	12	13	6-2267064-3
OBSOLETE	$\frac{4}{6}$	1.184	1.100	11	12	6-2267064-2
OBSOLETE	$\frac{4}{6}$	1.084	1.000	10	11	6-2267064-1
OBSOLETE	$\frac{4}{6}$.984	.900	9	10	6-2267064-0
	$\frac{4}{6}$.884	.800	8	9	5-2267064-9
OBSOLETE	$\frac{4}{6}$.784	.700	7	8	5-2267064-8
	$\frac{4}{6}$.684	.600	6	7	5-2267064-7
OBSOLETE	$\frac{4}{6}$.584	.500	5	6	5-2267064-6
OBSOLETE	$\frac{4}{6}$.484	.400	4	5	5-2267064-5
OBSOLETE	$\frac{4}{6}$.384	.300	3	4	5-2267064-4
OBSOLETE	$\frac{4}{6}$.284	.200	2	3	5-2267064-3
OBSOLETE	$\frac{4}{6}$.184	.100	1	2	5-2267064-2
OBSOLETE	$\frac{4}{6}$.084	-	-	1	5-2267064-1

FINISH	C	B	A	NO OF POS	PART NO
--------	---	---	---	-----------	---------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2014 NAGALAKSHMI K	TE TE Connectivity Ltd.		
DIMENSIONS: INCHES		CHK 03FEB2014 MILLER MICHAEL			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 03FEB2014 MILLER MICHAEL	NAME		
0 PLC ± -		PRODUCT SPEC	HEADER ASSY, MOD II, .100C/L, SINGLE ROW, RIGHT ANGLE, .025 SQUARE POST		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -			A2	00779	C=2267064
3 PLC ± .005			RESTRICTED TO		
4 PLC ± -			-		
ANGLES ± -		WEIGHT	SCALE 4:1 SHEET 2 OF 2 REV A1		
MATERIAL FINISH		CUSTOMER DRAWING			