





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	23OCT2017	KW	CS
	A1	ECR-17-017827	06DEC2017	RM	CS
	B	MAT. STRENGTH CHANGED, DRAWING UPDATED	07NOV2018	MW	CS




NOTES

Bemerkungen


- 1 2-5µm SILVER IN CONTACT AREA
2-5µm Silber in Kontaktbereich
- 2 0.1µm-3.0µm THK. TIN IN CRIMP AREA
0.1µm-3.0µm Sn im Crimpbereich

3. PACKAGING: PRODUCT REELED ON PLASTIC REEL WITH INTERLEAVING PAPER
3-4 REELS PER CARTON BOX. QUANTITY: 20000 PCS./REEL.
Verpackung: Spulenware auf Kunststoffspule mit Zwischenlagenpapier
3-4 Spulen pro Versandkarton. Stueckzahl: 20000 Teile/Spule


4. CONDITION AS DELIVERY
Auslieferungszustand




DETAIL Z
5:1



SECTION B-B
50:1



PLATING
Beschichtung



- 5 REVISION MARKING, MANUFACTURING LOCATION CODE AND DIE IDENTIFICATION
Revision Stempel, Produktionsstandort und Werkzeugkennzeichnung
- 6 LISTED WEIGHT INCLUDE THE CARRIER STRIP
Gewicht inklusive Traegerstreifen
- 7 APPLICATOR PN SEE IN APPLICATION SPEC. 114-94413
PN des Applicators siehe in Verarbeitungsspec. 114-94413
- 8 MICROSECTION FOR CRIMP INSPECTION HAVE TO BE
DONE ON SHOWN POSITION
Schliffbild zur Crimpueberwachung ist bei angezeigter
Position durchzufuehren

0.039 g	RG 174	0.14mm ²	1 2	CuSn	B	2298508-1
WEIGHT 6	CABLE TYPE	WIRE RANGE	FINISH	MATERIAL	REV	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. Weinberger 30AUG2017	 TE Connectivity			
DIMENSIONS: mm		CHK O. De Cloet 30AUG2017				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F. Schrettlinger 30AUG2017	NAME MATE-AX, PIN CENTER CONTACT 180 DEG RG 174			
		PRODUCT SPEC	-			
	MATERIAL	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO			
			A1 00779 C=2298508			
WEIGHT		RESTRICTED TO				
CUSTOMER DRAWING		SCALE 20:1 SHEET 1 of 1 REV B				
-	-	-	-			