



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-24-247111	05FEB2024	RK	CAS



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 THE TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 PRELIMINARY PART NUMBER NOT RELEASED FOR PRODUCTION.
- 4 HOUSING: FLAME RETARDANT THERMOPLASTIC
COLOR: BLACK
POSTS : PHOS. BRONZE
- 5 .000015 GOLD ON THE CONTACT AREA, MATTE TIN SOLDER AREA,
ALL OVER .000050 NICKEL.
- 6 .000003 GOLD OVER .000012 Pd/Ni ON THE CONTACT AREA, MATTE TIN SOLDER
AREA, ALL OVER .000050 NICKEL.



OBSOLETE	5	3.984	3.900	39	80	4-2267066-0
3	5	3.884	3.800	38	78	3-2267066-9
3	5	3.784	3.700	37	76	3-2267066-8
3	5	3.684	3.600	36	74	3-2267066-7
3	5	3.584	3.500	35	72	3-2267066-6
3	5	3.484	3.400	34	70	3-2267066-5
3	5	3.384	3.300	33	68	3-2267066-4
3	5	3.284	3.200	32	66	3-2267066-3
OBSOLETE	5	3.184	3.100	31	64	3-2267066-2
3	5	3.084	3.000	30	62	3-2267066-1
OBSOLETE	5	2.984	2.900	29	60	3-2267066-0
3	5	2.884	2.800	28	58	2-2267066-9
3	5	2.784	2.700	27	56	2-2267066-8
3	5	2.684	2.600	26	54	2-2267066-7
3	5	2.584	2.500	25	52	2-2267066-6
OBSOLETE	5	2.484	2.400	24	50	2-2267066-5
3	5	2.384	2.300	23	48	2-2267066-4
3	5	2.284	2.200	22	46	2-2267066-3
OBSOLETE	5	2.184	2.100	21	44	2-2267066-2
OBSOLETE	5	2.084	2.000	20	42	2-2267066-1
OBSOLETE	5	1.984	1.900	19	40	2-2267066-0
3	5	1.884	1.800	18	38	1-2267066-9
3	5	1.784	1.700	17	36	1-2267066-8
OBSOLETE	5	1.684	1.600	16	34	1-2267066-7
3	5	1.584	1.500	15	32	1-2267066-6
OBSOLETE	5	1.484	1.400	14	30	1-2267066-5
OBSOLETE	5	1.384	1.300	13	28	1-2267066-4
OBSOLETE	5	1.284	1.200	12	26	1-2267066-3
OBSOLETE	5	1.184	1.100	11	24	1-2267066-2
OBSOLETE	5	1.084	1.000	10	22	1-2267066-1
OBSOLETE	5	.984	.900	9	20	1-2267066-0
OBSOLETE	5	.884	.800	8	18	2267066-9
OBSOLETE	5	.784	.700	7	16	2267066-8
OBSOLETE	5	.684	.600	6	14	2267066-7
OBSOLETE	5	.584	.500	5	12	2267066-6
OBSOLETE	5	.484	.400	4	10	2267066-5
OBSOLETE	5	.384	.300	3	8	2267066-4
OBSOLETE	5	.284	.200	2	6	2267066-3
OBSOLETE	5	.184	.100	1	4	2267066-2
OBSOLETE	5	.084	-	-	2	2267066-1

FINISH	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: NAGALAKSHMI K 03FEB2014
CHK: MILLER MICHAEL 03FEB2014
APVD: MILLER MICHAEL 03FEB2014

TE Connectivity Ltd.

ASSEMBLY, MOD II, HEADER, DOUBLE ROW, .100 X .100 CL. VERTICAL, .025 SQUARE POSTS


SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=2267066 RESTRICTED TO: -

SCALE: 4:1 SHEET: 1 OF 2 REV: A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

OBSOLETE	△ ₆	3.984	3.900	39	80	9-2267066-0
△ ₃	△ ₆	3.884	3.800	38	78	8-2267066-9
△ ₃	△ ₆	3.784	3.700	37	76	8-2267066-8
△ ₃	△ ₆	3.684	3.600	36	74	8-2267066-7
△ ₃	△ ₆	3.584	3.500	35	72	8-2267066-6
△ ₃	△ ₆	3.484	3.400	34	70	8-2267066-5
△ ₃	△ ₆	3.384	3.300	33	68	8-2267066-4
△ ₃	△ ₆	3.284	3.200	32	66	8-2267066-3
OBSOLETE	△ ₆	3.184	3.100	31	64	8-2267066-2
△ ₃	△ ₆	3.084	3.000	30	62	8-2267066-1
OBSOLETE	△ ₆	2.984	2.900	29	60	8-2267066-0
△ ₃	△ ₆	2.884	2.800	28	58	7-2267066-9
△ ₃	△ ₆	2.784	2.700	27	56	7-2267066-8
△ ₃	△ ₆	2.684	2.600	26	54	7-2267066-7
△ ₃	△ ₆	2.584	2.500	25	52	7-2267066-6
OBSOLETE	△ ₆	2.484	2.400	24	50	7-2267066-5
△ ₃	△ ₆	2.384	2.300	23	48	7-2267066-4
△ ₃	△ ₆	2.284	2.200	22	46	7-2267066-3
OBSOLETE	△ ₆	2.184	2.100	21	44	7-2267066-2
OBSOLETE	△ ₆	2.084	2.000	20	42	7-2267066-1
OBSOLETE	△ ₆	1.984	1.900	19	40	7-2267066-0
OBSOLETE	△ ₆	1.884	1.800	18	38	6-2267066-9
△ ₃	△ ₆	1.784	1.700	17	36	6-2267066-8
OBSOLETE	△ ₆	1.684	1.600	16	34	6-2267066-7
△ ₃	△ ₆	1.584	1.500	15	32	6-2267066-6
OBSOLETE	△ ₆	1.484	1.400	14	30	6-2267066-5
OBSOLETE	△ ₆	1.384	1.300	13	28	6-2267066-4
OBSOLETE	△ ₆	1.284	1.200	12	26	6-2267066-3
OBSOLETE	△ ₆	1.184	1.100	11	24	6-2267066-2
OBSOLETE	△ ₆	1.084	1.000	10	22	6-2267066-1
OBSOLETE	△ ₆	.984	.900	9	20	6-2267066-0
OBSOLETE	△ ₆	.884	.800	8	18	5-2267066-9
OBSOLETE	△ ₆	.784	.700	7	16	5-2267066-8
OBSOLETE	△ ₆	.684	.600	6	14	5-2267066-7
OBSOLETE	△ ₆	.584	.500	5	12	5-2267066-6
OBSOLETE	△ ₆	.484	.400	4	10	5-2267066-5
OBSOLETE	△ ₆	.384	.300	3	8	5-2267066-4
OBSOLETE	△ ₆	.284	.200	2	6	5-2267066-3
OBSOLETE	△ ₆	.184	.100	1	4	5-2267066-2
OBSOLETE	△ ₆	.084	-	-	2	5-2267066-1

FINISH C B A NO OF POS ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2014 NAGALAKSHMI K	 TE Connectivity Ltd.	
DIMENSIONS: INCHES		CHK 03FEB2014 MILLER MICHAEL		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 03FEB2014 MILLER MICHAEL	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC	ASSY, MOD II, HEADER, DOUBLE ROW, .100 X .100 CL. VERTICAL, .025 SQUARE POSTS	
MATERIAL		APPLICATION SPEC	SIZE A2	CAGE CODE 00779
FINISH		WEIGHT -	DRAWING NO C-2267066	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 2 OF 2
			REV A1	