



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECR-17-012757	31AUG2017	GZ	IY
	A1	ECR-19-002579	18FEB2019	GZ	EJ





1. BULK PACKAGING
2. TPA AND CPA DELIVERY CONDITION: IN PRE LOCK POSITION
SHOULD TPA UNEXPECTED BECOME ENGAGED, PLEASE SEE APPLICATION SPECIFICATION FOR DIRECTION OF DISENGAGING TPA

- A1

3

 AVAILABLE TERMINALS AS TABLE SHOWN
4. INTERFACE DRAWING: 114-101051
5. TE ASSY NO. SEE TABLE

1-2295393-1 AS SHOWN
WITH WIRE DRESS



0-2295393-1 AS SHOWN
WITHOUT WIRE DRESS

















1452503-1	1.0~1.5mm ²	PRE-TIN
1670144-1	0.5~0.75mm ²	PRE-TIN
(1534594-1)	0.25~0.35mm ²	PRE-TIN
TE PN	WIRE SIZE RANGE (REF)	FINISH
3 COMPONENT: TERMINAL 1.2 mm (APPLICATION: 114-18464)		

1718475-1	>2.5 ~4.0mm ²	PRE-TIN
1719840-1	>1.0 ~2.5mm ²	PRE-TIN
1719838-1	0.75~1.0mm ²	PRE-TIN
1563719-1	0.5 mm ²	PRE-TIN
(1719836-1)	0.2~0.35mm ²	PRE-TIN
TE PN	WIRE RANGE (mm ²)	FINISH
3 COMPONENT: TERMINAL 2.8 mm (APPLICATION: 114-18718)		

YES	1-2295393-4 (NOT TOOLED)	E	9.261	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	(GRAY)	I	1
	1-2295393-3 (NOT TOOLED)	D	9.261	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	(BLUE)	I	1
	1-2295393-2	B	9.261	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	PINK	I	1
	1-2295393-1	A	9.261	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	BLACK	I	1
NO	2295393-4 (NOT TOOLED)	E	8.451	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	(BLUE)	I	1
	2295393-3 (NOT TOOLED)	D	8.451	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	(GRAY)	I	1
	2295393-2	B	8.451	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	PINK	I	1
	2295393-1	A	8.451	CPA	PBT-GF15	RED	I	3
				TPA	PBT-GF30	RED	I	2
				HOUSING	PBT-GF30	BLACK	I	1
WIRE DRESS	TE ASSY NO	CODE	WEIGHT (G)	DESCRIPTION	MATERIAL	COLOR	QTY	POSN

THIS DRAWING IS A CONTROLLED DOCUMENT				DWN	08OCT2015		TE TE Connectivity						
				CHK	08OCT2015								
				APVD	10OCT2015								
				NAME									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME 16POS PLUG ASSY UNSEALED, HYBRID, BCM							
mm				108-101447									
				APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO							
				114-101044									
MATERIAL		FINISH		WEIGHT		A1		-		C=2295393		-	
CUSTOMER DRAWING				SCALE		3:1		SHEET		1 OF 2		REV A1	

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-

 	 	 	 	 	 	 	 
0-2295393-1	0-2295393-2	0-2295393-3	0-2295393-4	1-2295393-1	1-2295393-2	1-2295393-3	1-2295393-4
BLACK	PINK	(NOT TOOLED)	(NOT TOOLED)	BLACK	PINK	(NOT TOOLED)	(NOT TOOLED)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: G. ZHU


CHK: G. ZHU

APVD: S. WANG

08OCT2015
08OCT2015
10OCT2015

DIMENSIONS:

mm



0 PLC ±0.3

1 PLC ±0.15

2 PLC ±0.15

3 PLC ±0.15

4 PLC ±0.15

ANGLES ±2°

FINISH

PRODUCT SPEC

108-101447

APPLICATION SPEC

114-101044

WEIGHT

CUSTOMER DRAWING

NAME

16POS PLUG ASSY
UNSEALED, HYBRID, BCM

SIZE

A1

CAGE CODE

-

DRAWING NO

C=2295393

RESTRICTED TO

-

SCALE

3:1

SHEET

2

OF

2

REV

A1