









NOTES
Bemerkungen

- PACKAGING: PRODUCT REELED ON CORRUGATED REEL WITH INTERLEAVING PAPER
THREE REELS PER CORRUGATED SHIPPING BOX. QUANTITY: 3500 PCS./REEL.
Verpackung: Spulenware auf Wellpappespule mit Zwischenlagenpapier
Drei Spulen pro Versandkarton. Stueckzahl: 3500 Teile/Spule
- CONDITION AS DELIVERY
Auslieferungszustand



- A4

3

TE CONNECTIVITY LOGO
TE Connectivity Logo
- 4

REVISION STATE AND DATE CODE
Revisionsstatus und Datumscode
- 5

LISTED WEIGHT INCLUDE THE CARRIER STRIP AND THE DIELECTRIC
Gewicht inklusive Traegerstreifen und Dielektrikum
- 6

APPLICATOR PN SEE IN APPLICATION SPEC. 114-94413
PN des Applicators siehe in Verarbeitungsspec. 114-94413
- 7

ALLOWED AREA FOR CONTACT GRIPPING
FOR CABLE TERMINATION
Zulaessiger Bereich zum Greifen des
Kontaktes bei der Kabelverarbeitung
- A4

8

DURING THE CABLE ASSEMBLY PROCESS, THE CONTACT MAY BE
LOADED WITH MAX. 30 N IN AXIAL DIRECTION.
THE INSERTION FORCE INTO THE HOUSING MAY NOT EXCEED 60 N.
Im Kabelmontageprozess darf der Kontakt an gezeigter
Stelle axial mit max. 30 N belastet werden.
Die Montagekraft in die Gehäussekammer darf max. 60 N betragen.
- 9

INSERTION AREA FOR GAUGE PIN DIA 2.8-0.005. FORCE 10N max.
Einfuehrbereich fuer Pruefdorn Ø2.8-0.005. Pruefkraft 10N max.

SUB-ASSEMBLY PIN CONTACT	Pin Outer Contact	CuSn	Sn (0.8-3µm)	A	2298506-1
	Dielectric	PBT	blue RAL 5012 similar		
DESCRIPTION Benennung		MATERIAL Werkstoff	SURFACE Oberflaeche	REV	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. Weinberger	28AUG2017	TE Connectivity	
DIMENSIONS:		CHK O. de Cloet	28AUG2017		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. Schrettlinger	28AUG2017	NAME	
	0 PLC ±0.2	PRODUCT SPEC		STAMPED OUTER CONTACT	
	1 PLC ±0.1	APPLICATION SPEC		MALE 180 DEGREES MATE-AX. RG174	
	2 PLC ±0.1	WEIGHT		SIZE	
	3 PLC ±	0.504g/5		CAGE CODE	
MATERIAL	4 PLC ±	CUSTOMER DRAWING		DRAWING NO	
	ANGLES FINISH			100779	
-	-			©=2298506	
-	-			SCALE	
				10:1	
				SHEET	
				1 OF 1	
				REV	
				A4	