


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		ECO-20-010687: SM FORMAT UPDATED	31JUL2020	SS	GL



1. SEE SHEET 2 FOR WIRING SCHEMATIC.
2. ALL MATERIALS, COMPONENTS AND PROCESSES SHALL COMPLY WITH TEC-138-702. (CONTAIN NO BANNED OR RESTRICTED SUBSTANCES).
3. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
4. CABLE ASSEMBLY 100% TESTED FOR OPENS, SHORTS, AND PROPER EEPROM PROGRAM.

△ LABEL INFORMATION: -1 SHOWN.

TE

QSFP-DD - (8) SFP
2327689-1
10M 28AWG
PPPPPLYWWSSS
MADE IN ---

TE LOGO

TE PART NUMBER

LENGTH & WIRE GAUGE

SERIAL NUMBER

INCLUDES PN, MANUFACTURING LOCATION AND DATE CODE

SERIAL NUMBER

BARCODE

COUNTRY OF ORIGIN

2.5M 28AWG	2500±30	2327689-4
2.0M 28AWG	2000±30	2327689-3
1.5M 28AWG	1500±25	2327689-2
1.0M 28AWG	1000±20	2327689-1
CONFIGURATION	"L"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 06AUG2018	TE Connectivity	
DIMENSIONS:		CHK K. STAUFFER 06AUG2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K. STAUFFER 06AUG2018	NAME CABLE ASSEMBLY, 28 AWG QSFP-DD TO (8) SFP56	
0 PLC ±	1 PLC ±	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
2 PLC ±	3 PLC ±	APPLICATION SPEC	RESTRICTED TO	
4 PLC ±	ANGLES ±	WEIGHT	A 00779 C=2327689	
FINISH			RESTRICTED CUSTOMER	
MATERIAL			SCALE 5:1 SHEET 1 OF 2 REV B	

