









2303088-1 AS SHOWN

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
B1		DESIGN CHANGE ON 32 POS SERIE 2303088-1	08MAR2017	RS
B2		PAGE 2 REMOVED, DETAILS ADDED	28SEP2017	MaS
B3		CHANGE OF TOLERANCES	09MAR2018	RS
B4		20POS/ 32POS CODING A+B ADDED	25MAR2020	MaS





- NOTES:
Bemerkungen:
- 1 TE-PART. SEE TABLE
TE-Teilenummer, siehe Tabelle
- 2 MATERIAL MARKING
Materialbezeichnung
- 3 PRODUCTION DATE CODE
Produktionsdatumsuhr
- 4 MARKING OF MOLD CAVITY
Formnestnummer
- 5 CONTACT CAVITY IDENTIFICATION NUMBER
Identifikationsnummer der Kontaktkammer
- 6 TE-LOGO
TE-Logo
- 7 PACKAGING: BULK IN BOX WITH A BAG
Verpackung: Schuetftgut im Beutel und Karton
- 8 ONLY APPLICABLE WITH CONTACT PN: 2291853
Zu verwenden nur mit dem Kontakt PN: 2291853
- 9 SLOT-DIMENSION FOR FOIL WITH CONTACTS
Masse vom Schlitz fuer angecrimpfte Folie
- 10 APP. AND PROD. SPEC WILL ONLY BE PUBLISHED
AFTER COPMLETION OF VALIDATION.
App. und Prod. Spez. werden erst nach
abgeschlossener Validierung veroeffentlicht.
- 11 DIMENSIONS OF THE CONTACT DETECTION WINDOWS
Masse der Kontaktidentifizierungsfenster
- 12 FOR 32 POS REC HSG 14.8 +0.4/-0.2 ALLOWED
Fuer 32 pol Rec Gehaeuse 14.8 +0.4/-0.2 zulaessig
- 13 TE-REVISION. SEE TABLE
TE-Revision, siehe Tabelle

SERIES				
SKETCH SCALE 1:1				
NUMBER OF POS. SHOWN ON PAGE	32 1	20 2	8 2	
CONNECTOR TE-PART NUMBER	2303088-1	2303088-2	2303088-3	2365086-1
TE-PART REVISION	B	B	B	A
CODING	Z	A	B	A
COLOR	WATERBLUE	BLACK	NATURAL	BLACK
SIMILAR RAL	5021	9011	1015	9011
MATERIAL	PBT-GF10			
DIM "A"	33.1	22.3	11.5	
DIM "B"	15.3	9.9	4.5	
DIM "C"	17	11	5	
DIM "D"	30.6	19.8	9	
DIM "E"	35±0.13	23.9±0.11	13.4±0.1	
DIM "F"	30.9	20.1	9.3	
DIM "G"	2.7	2.1	1.5	
DIM "H"	33.7±0.13	22.75±0.11	12.1±0.1	
DIM "I"	14.33±0.1	8.49±0.1	3.48 +0.2 -0.05	B3
SUITABLE HEADER	X-2177419-X X-2177748-X	0-/4-2177367-X 0-/4-2177766-X	X-2177372-X X-2177768-X	
GENERIC INTERFACE PART NUMBER	114-20160-150	114-20160-90	114-20160-40	
WEIGHT APP.	3 g	2 g	1 g	





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.Schmitt CHK R.Stab APVD S.Reichel	08JUN2016 08JUN2016 26JUL2016
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-94541 APPLICATION SPEC 114-94437	NAME 8/ 20/ 32POS.NANOMOS. FPC/FFC, REC HSG, UNSLD
MATERIAL SEE TABLE siehe Tabelle	SEE TABLE	WEIGHT SEE TABLE	SIZE A1
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 2
		REV B4	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

8 POS RECEPTACLE HOUSING
2303089-1



20 POS RECEPTACLE HOUSING
2365086-1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M.Schmitt

08JUN2016

CHK

R.Stab

08JUN2016

APVD

S.Reichel

26JUL2016

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±

±

±

±

±

±

MATERIAL

SEE TABLE

siehe Tabelle

WEIGHT

SEE TABLE

CUSTOMER DRAWING

PRODUCT SPEC

108-94541

APPLICATION SPEC

116-94437

NAME

8 / 20 / 32POS.NANOMOS.
FPC/FFC, REC HSG, UNSLD

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

5:1

SHEET

2

OF

2

REV

B4

TE Connectivity