




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	30EC2018	DS	HL



- 1 MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING: THERMALPLASTIC,UL 94V-0
- 2 FINISH: SIGNAL AND GROUND CONTACTS:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF
PRODUCT SPECIFICATION 108-60115; BASED ON TELCORDIA
GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5 um MIN MATTE
TIN OVER BASE PLATING
- 3 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 5 CONTACT AREA LUBRICATED WITH BELLCORE
APPROVED LUBRICANT. TECHNICAL REFERENCE:
GR-1217-CORE, ISSUE 2, DECEMBER 2008.
- 6 RECOMMENDED THRU HOLE DIAMETER AND PLATING THICKNESSES PLEASE
REFER TO APPLICATION SPEC 114-13059



RECOMMENDED PCB LAYOUT
=====

2329186-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID SHEN 7DEC2017	TE Connectivity	
		CHK ALEX SHOAL 7DEC2017		
DIMENSIONS:		APVD HOPE LU 8DEC2017	NAME ASSEMBLY DRAWING HM-eZD+ VERTICAL,HEADER,2PAIRS 10COLUMNS	
mm		PRODUCT SPEC		
		108-60115	SIZE CAGE CODE DRAWING NO	
		APPLICATION SPEC		
MATERIAL		114-13059	A100779C=2329186	
		WEIGHT		
		CUSTOMER DRAWING	SCALE 5:1 SHEET 1 OF 1 REV A	