



1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC
 POLYESTER(94V-0), COLOR: BLACK
 CONTACT: COPPER ALLOY
 RETENTION LEG: PRE-TIN COPPER ALLOY



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		INITIAL	19MAR2018	F.Z R.B
B		REVISED	10AUG2018	F.Z R.B
BI		REVISED	05FEB2021	F.Z R.B

2. FINISH(ALL OVER): NICKEL PL. 1.27μmMIN
 3. FINISH(ALL OVER): TIN PLATED 1.0μmMIN AFTER 2

4. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
 5. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".



RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
 PC BOARD THICKNESS : 1.0~1.6±0.1



POS	KEY	n	A	B	C	FINISH	PART NO
40	X	19	38.0	41.0	42.6	TIN PLATED	1-2329463-0
34	Y	16	32.0	35.0	36.6	TIN PLATED	2-2329463-7
34	X	16	32.0	35.0	36.6	TIN PLATED	1-2329463-7
32	X	15	30.0	33.0	34.6	TIN PLATED	1-2329463-6
30	X	14	28.0	31.0	32.6	TIN PLATED	1-2329463-5
28	X	13	26.0	29.0	30.6	TIN PLATED	1-2329463-4
26	X	12	24.0	27.0	28.6	TIN PLATED	1-2329463-3
24	X	11	22.0	25.0	26.6	TIN PLATED	1-2329463-2
22	X	10	20.0	23.0	24.6	TIN PLATED	1-2329463-1

34POS(X-KEY): 1-2329463-7

34POS(Y KEY: 2-2329463-7)
 SYMMETRY FOR KEY ARRANGEMENT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±3°	DWN FISHER ZHU 08MAR2018	TE Connectivity DYNAMIC D1100 HEADER ASSY V-TYPE, TIN PLATED, 22~40POS
	1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.001±	CHK RICK BIAN 08MAR2018	
MATERIAL 1	FINISH 2-3	APVD RICK BIAN 08MAR2018	
APPLICATION SPEC 108-78298 114-5377		NAME	
WEIGHT INTERFACE DRAWING		SIZE A2	CAGE CODE 00779
		DRAWING NO C-2329463	RESTRICTED TO -
		SCALE 2:1	SHEET 1 OF 2
			REV BI

4













3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-		SEE SHEET 1	-	-



22POS(X-KEY): 1-2329463-1

26POS(X-KEY): 1-2329463-3

28POS(X-KEY): 1-2329463-4

32POS(X-KEY): 1-2329463-6

THIS DRAWING IS A CONTROLLED DOCUMENT		DWN FISHER ZHU 08MAR2018	TE Connectivity		
DIMENSIONS: mm		CHK RICK BIAN 08MAR2018			
MATERIAL		APVD RICK BIAN 08MAR2018	NAME DYNAMIC D1100 HEADER ASSY V-TYPE, TIN PLATED, 22-40POS		
TO DIMENSIONS UNLESS OTHERWISE SPECIFIED: 0. PLG ±0.5 2. PLG ±0.13 3. PLG ±0.013 4. PLG ±0.0001 ANGLES ± FINISH		PRODUCT SPEC 108-78298	SIZE A2	CAGE CODE 00779	DRAWING NO G-2329463
SEE SHEET 1 OF 2		APPLICATION SPEC 114-5377	RESTRICTED TO	-	
1		WEIGHT		INTERFACE DRAWING	
2-3		SCALE		2:1	
		SHEET		2 OF 2	
		REV		B1	