



THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		-	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	14JUL2016	FL	SY


8.55			73.15	71.35	89.0	70	164	NATURE	30u"	4-2306645-8
									15u"	4-2306645-7
									G/F	4-2306645-6
8.6								BLACK	30u"	4-2306645-5
									15u"	4-2306645-4
									G/F	4-2306645-3
5.4			40.15	38.35	56.0	37	98	NATURE	30u"	4-2306645-2
									15u"	4-2306645-1
									G/F	4-2306645-0
5.45								BLACK	30u"	3-2306645-9
									15u"	3-2306645-8
									G/F	3-2306645-7
3.8			23.15	21.35	39.0	20	64	NATURE	30u"	3-2306645-6
									15u"	3-2306645-5
									G/F	3-2306645-4
3.85								BLACK	30u"	3-2306645-3
									15u"	3-2306645-2
									G/F	3-2306645-1
2.53								NATURE	30u"	3-2306645-0
									15u"	2-2306645-9
									G/F	2-2306645-8
2.55			9.15	7.35	25.0	6	36	BLACK	30u"	2-2306645-7
									15u"	2-2306645-6
									G/F	2-2306645-5
8.55			73.15	71.35	89.0	70	164	NATURE	30u"	2-2306645-4
									15u"	2-2306645-3
									G/F	2-2306645-2
8.6								BLACK	30u"	2-2306645-1
									15u"	2-2306645-0
									G/F	1-2306645-9
5.4								NATURE	30u"	1-2306645-8
									15u"	1-2306645-7
									G/F	1-2306645-6
5.45			40.15	38.35	56.0	37	98	BLACK	30u"	1-2306645-5
									15u"	1-2306645-4
									G/F	1-2306645-3
3.8								NATURE	30u"	1-2306645-2
									15u"	1-2306645-1
									G/F	1-2306645-0
3.85			23.15	21.35	39.0	20	64	BLACK	30u"	2306645-9
									15u"	2306645-8
									G/F	2306645-7
2.53								NATURE	30u"	2306645-6
									15u"	2306645-5
									G/F	2306645-4
2.55			9.15	7.35	25.0	6	36	BLACK	30u"	2306645-3
									15u"	2306645-2
									G/F	2306645-1
WEIGHT(g)	PACKAGING	DIM. L	DIM.D	DIM.C	DIM.B	DIM.A	POS.	HOUSING COLOR	MIN GOLD THICKNESS	PART NUMBER

5.4	T&R WITH MYLAR	3.1	40.15	38.35	56.0	37	98	NATURE	30u”	9-2306645-2
5.45								BLACK	15u”	9-2306645-1
									G/F	9-2306645-0
			3.8	23.15	21.35	39.0	20		64	NATURE
15u”								8-2306645-8		
G/F								8-2306645-7		
3.85			BLACK	30u”	8-2306645-6					
				15u”	8-2306645-5					
				G/F	8-2306645-4					
2.53			9.15	7.35	25.0	6	36	NATURE	30u”	8-2306645-3
									15u”	8-2306645-2
									G/F	8-2306645-1
2.55		BLACK	30u”	8-2306645-0						
			15u”	7-2306645-9						
			G/F	7-2306645-8						
5.4		2.3	40.15	38.35	56.0	37	98	NATURE	30u”	7-2306645-7
									15u”	7-2306645-6
									G/F	7-2306645-5
5.45		BLACK	30u”	6-2306645-8						
			15u”	6-2306645-7						
			G/F	6-2306645-6						
3.8		23.15	21.35	39.0	20	64	NATURE	30u”	6-2306645-5	
								15u”	6-2306645-4	
								G/F	6-2306645-3	
3.85		BLACK	30u”	6-2306645-2						
			15u”	6-2306645-1						
			G/F	6-2306645-0						
2.53		9.15	7.35	25.0	6	36	NATURE	30u”	5-2306645-9	
								15u”	5-2306645-8	
								G/F	5-2306645-7	
2.55		BLACK	30u”	5-2306645-6						
			15u”	5-2306645-5						
			G/F	5-2306645-4						
								BLACK	30u”	5-2306645-3
									15u”	5-2306645-2
									G/F	5-2306645-1
WEIGHT(g)	PACKAGING	DIM. L	DIM.D	DIM.C	DIM.B	DIM.A	POS.	HOUSING COLOR	MIN GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	14JUL2016	 TE Connectivity	
		CHK	14JUL2016		
		APVD	14JUL2016		
		NAME			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PCI EXPRESS CONNECTOR VERTICAL, DIP TYPE, CUT-END WALL	
		0 PLC	± -	-	
		1 PLC	± -	-	
		2 PLC	± -	-	
		3 PLC	± -	-	
		4 PLC	± -	-	
		ANGLES	± -	-	
		FINISH		-	
MATERIAL		WEIGHT		-	
SEE NOTE		SEE NOTE		-	
		CUSTOMER DRAWING		-	
		SCALE		-	
		SHEET		1 of 5	
		REV		A	



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



164	70.0	73.15	72.15	A1,B17,B31,B48,B81
98	37.0	40.15	39.15	A1,B17,B31,B48
64	20.0	23.15	22.15	A1,B17,B31
36	6.0	9.15	8.15	A1,B17
POS.	DIM. F	DIM. G	DIM. H	"K"

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
FRED LIU
14JUL2016

CHK
ALEX SHOAL
14JUL2016

APVD
STEVEN YIN
14JUL2016

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

-

NAME

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2306645

RESTRICTED TO

TE Connectivity

PCI EXPRESS CONNECTOR
VERTICAL, DIP TYPE, CUT-END WALL

SCALE
-

SHEET
3 of 5

REV
A



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D


C

B

A



- NOTES :
- MATERIAL :
TRAY: PVC, COLOR: TRANSPARENT.
CARTON: CORRUGATED FIBER
BOX: CORRUGATED FIBER
TRANSPARENT BAG: PE
 - DIMENSION :
TRAY: SEE DRAWING
CARTON: SEE DRAWING
BOX: SEE DRAWING
TRANSPARENT BAG: 480mm*350mm*0.06mm
600mm*590mm*0.06mm
 - QUANTITY: SEE TABLE
 - WEIGHT: SEE TABLE
 - EACH BAG SHALL BE INCLUDED:
* DESICCANT



9.7 KG	7.7 KG	30	10	3	900	164
8.6 KG	6.6 KG	40	10	3	1200	98
8.9 KG	6.9 KG	60	10	3	1800	64
7.4 KG	5.4 KG	70	10	3	2100	36
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ CARTON	CARTON/ BOX	PCS/ BOX	POS

2306645

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

SEE NOTE

DWN
FRED LIU
14JUL2016

CHK
ALEX SHOAL
14JUL2016

APVD
STEVEN YIN
14JUL2016

PRODUCT SPEC

APPLICATION SPEC

WEIGHT
SEE TABLE

CUSTOMER DRAWING

TE Connectivity

PCI EXPRESS CONNECTOR
VERTICAL, DIP TYPE, CUT-END WALL

SIZE
A2

CAGE CODE
00779




DRAWING NO
C=2306645

RESTRICTED TO
-

SCALE
-

SHEET
4 OF 5

REV
A



92.4	88.4	60.0	57.6	88.0	84.4	42.2±0.3	5.6 Kg	2.8 Kg	170	3	510	98P
60.4	56.4	43.0	40.6	56.0	52.4	26.2±0.15	5.4 Kg	2.6 Kg	170	4	680	64P
60.4	56.4	29.0	26.6	56.0	52.4	26.2±0.15	4.5 Kg	1.7 Kg	170	4	680	36P
DIM. G	DIM. F	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	GROSS WEIGHT	NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	POSITION NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU 14JUL2016 CHK ALEX SHOAL 14JUL2016 APVD STEVEN YIN 14JUL2016		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME PCI EXPRESS CONNECTOR VERTICAL, DIP TYPE, CUT-END WALL -			
		PRODUCT SPEC - APPLICATION SPEC -					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE		SEE NOTE		WEIGHT	A2	00779	 2306645 -
CUSTOMER DRAWING				SCALE	-	SHEET	5 of 5
				REV	A		