



REVISIONS					
P	LTN	DESCRIPTION	DATE	DWN	APVD
3		REVISED NOTES 4 AND 5 PER ECO-20-013264	12OCT2020	REH	MS



- SEE SHEET 2 FOR WIRING SCHEMATIC.
- ALL MATERIALS, COMPONENTS AND PROCESSES SHALL COMPLY WITH TEC-138-702. (CONTAIN NO BANNED OR RESTRICTED SUBSTANCES).
- NO REACH SVHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SVHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
- CABLE ASSEMBLIES ARE 100% TESTED FOR OPENS, SHORTS, HI-POT, AND PROPER EEPROM PROGRAM.

△ LABEL INFORMATION: -1 SHOWN.



THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: T. SMITH 06JUN2018	TE Connectivity
DIMENSIONS: mm		CHK: K. STAUFFER 06JUN2018	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: K. STAUFFER 06JUN2018	NAME: CABLE ASSEMBLY, 26 AWG OSFP TO (8) SFP56 PRODUCT SPEC: - APPLICATION SPEC: -
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		WEIGHT: - MATERIAL: - FINISH: -	
CUSTOMER DRAWING		SIZE: A 00779 C=2336064	RESTRICTED TO: -
SCALE: 5:1		SHEET: 1 OF 2	REV: 3

REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
-		SEE SHEET 1	-	-

P1 (OSFP)			P2 (SFP56)	
GND				GND
TX1+	59	↔	13	RX1+
TX1-	58	↔	12	RX1-
GND				GND
RX1+	29	↔	18	TX1+
RX1-	28	↔	19	TX1-
GND				GND

P1 (OSFP)			P3 (SFP56)	
GND				GND
TX2+	2	↔	13	RX1+
TX2-	3	↔	12	RX1-
GND				GND
RX2+	32	↔	18	TX1+
RX2-	33	↔	19	TX1-
GND				GND

P1 (OSFP)			P4 (SFP56)	
GND				GND
TX3+	56	↔	13	RX1+
TX3-	55	↔	12	RX1-
GND				GND
RX3+	26	↔	18	TX1+
RX3-	25	↔	19	TX1-
GND				GND

P1 (OSFP)			P5 (SFP56)	
GND				GND
TX4+	5	↔	13	RX1+
TX4-	6	↔	12	RX1-
GND				GND
RX4+	35	↔	18	TX1+
RX4-	36	↔	19	TX1-
GND				GND

P1 (OSFP)			P6 (SFP56)	
GND				GND
TX5+	53	↔	13	RX1+
TX5-	52	↔	12	RX1-
GND				GND
RX5+	23	↔	18	TX1+
RX5-	22	↔	19	TX1-
GND				GND

P1 (OSFP)			P7 (SFP56)	
GND				GND
TX6+	8	↔	13	RX1+
TX6-	9	↔	12	RX1-
GND				GND
RX6+	38	↔	18	TX1+
RX6-	39	↔	19	TX1-
GND				GND



P1 (OSFP)			P8 (SFP56)	
GND				GND
TX7+	50	↔	13	RX1+
TX7-	49	↔	12	RX1-
GND				GND
RX7+	20	↔	18	TX1+
RX7-	19	↔	19	TX1-
GND				GND

P1 (OSFP)			P9 (SFP56)	
GND				GND
TX8+	11	↔	13	RX1+
TX8-	12	↔	12	RX1-
GND				GND
RX8+	41	↔	18	TX1+
RX8-	42	↔	19	TX1-
GND				GND

WIRING PATTERN

THIS PRODUCT HAS NOT COMPLETED VALIDATION AND QUALIFICATION TESTING

PRELIMINARY NOT RELEASED FOR PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 06JUN2018 CHK K. STAUFFER 06JUN2018 APVD K. STAUFFER 06JUN2018	 TE Connectivity
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	NAME CABLE ASSEMBLY, 26 AWG OSFP TO (8) SFP56 PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO A 00779 C=2336064	
MATERIAL	FINISH	WEIGHT	RESTRICTED TO CUSTOMER DRAWING SCALE 5:1 SHEET 2 OF 2 REV 3