





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
 CONTACT: COPPER ALLOY
 RETENTION LEG: PRE-TIN COPPER ALLOY

REVISONS				DATE	DWN	APVD
P	LTR	DESCRIPTION				
A		INITIAL	05DEC2018	F.Z	R.B	

- 2. FINISH(ALL OVER): NICKEL PL. 1.27μmMIN
- 3. FINISH(ALL OVER): TIN PL. 1.0μmMIN AFTER 2
- 4. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.



RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
 PC BOARD THICKNESS : 1.0~1.6±0.1

AS SHOWN : 1-2348455-0 (20POS: X-KEY)
 ONLY 4POS----SEE SHEET 2 OF 3

20	X	9	22.5	26.0	27.6	1-2348455-0
12	X	5	12.5	16.0	17.6	1-2348455-6
8	X	3	7.5	11.0	12.6	1-2348455-4
6	X	2	5.0	8.5	10.1	1-2348455-3
4	X	1	2.5	6.0	7.6	1-2348455-2
POS KEY	n	A	B	C		PART NO


1-2348455-0
 (20POS: X-KEY)

THIS DRAWING IS A CONTROLLED DOCUMENT.


DWN FISHER, ZHU 05DEC2018	TE Connectivity
CHK RICK, BIAN 05DEC2018	
APVD RICK, BIAN 05DEC2018	
PRODUCT SPEC	
DIMENSIONS: mm	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (H-TYPE) TIN PLATING 4-20POS
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±3°	SIZE CAGE CODE DRAWING NO RESTRICTED TO
0-PLC ±0.5	108-78298
1-PLC ±0.5	114-5377
2-PLC ±0.13	WEIGHT -
3-PLC ±0.013	RESTRICTED CUSTOMER
4-PLC ±0.0001	SCALE 6:1
ANGLES ±	SHEET 1 OF 3
FINISH	REV A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-	-	-







1-2348455-2
(4POS: X-KEY)




RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
 PC BOARD THICKNESS : 1.0~1.6±0.1

ONLY 4POS




THIS DRAWING IS A CONTROLLED DOCUMENT		DWN FISHER, ZHU 05DEC2018	TE Connectivity	
DIMENSIONS: mm		CHK RICK BIAN 05DEC2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RICK BIAN 05DEC2018	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (H-TYPE) TIN PLATING 4-20POS	
1 PLC ±		PRODUCT SPEC 108-78298	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
2 PLC ±		APPLICATION SPEC 114-5377	A200779 C-2348455	
3 PLC ±		WEIGHT	SCALE 6:1 SHEET 2 OF 3 REV A	
4 PLC ±		RESTRICTED CUSTOMER		
ANGLES ±				
FINISH				


LOC		DIST		REVISIONS			
P	LTR	DATE	DWN	APVD			
-	-	-	-	-	SEE SHEET 1		









1-2348455-3
(6POS:X-KEY)



1-2348455-4
(8POS:X-KEY)



1-2348455-6
(12POS:X-KEY)



THIS DRAWING IS A CONTROLLED DOCUMENT		DWN FISHER, ZHU 05DEC2018	 TE Connectivity
DIMENSIONS: mm		CHK RICK, BIAN 05DEC2018	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RICK, BIAN 05DEC2018	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (H-TYPE) TIN PLATING 4-20POS
1 PLC ±		PRODUCT SPEC 108-78298	SIZE A200779
2 PLC ±		APPLICATION SPEC 114-5377	CAGE CODE C-2348455
3 PLC ±		WEIGHT -	DRAWING NO -
4 PLC ±		RESTRICTED CUSTOMER	RESTRICTED TO A
ANGLES ±		SCALE 6:1	SHEET 3 OF 3
FINISH			REV A