


VARIANT 1 - WITHOUT CPA





2310137-1 CODING "A" AS SHOWN

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	A	INITIAL RELEASE	17MAY2019	MS CS
	B	HSG REV / CODING TOL UPD TO. ADDED NOTE 10	17JUL2020	MS CS
	B1	TOLERANCES UPDATED	29MAR2023	JJ CS


SCALE 2:1



- 1
- ONLY THE GERMAN LANGUAGE SHALL BE BINDING
Massgebend ist der deutsche Text
- 2
- DETAILS OF DESIGN ARE LEFT TO TE CONNECTIVITY
Einzelheiten der Ausführung bleiben TE CONNECTIVITY ueberlassen
- 3
- PACKAGING: BULK IN CARDBOARD BOX
Verpackung: Schuetftgut in Karton
- 4
- TE ORDER NO. X-2310137-Y SEE TABLE
TE-Bestellnummer X-2310137-Y siehe Tabelle
- 5
- CONDITION AS SUPPLIED: TPA IN PRE-LOCKED POSITION.
IF IN ENDLOCKING POSITION OR LOST AFTER TRANSPORTATION.
REWORK ALLOWED IN ACCORDANCE TO APPLICATION SPECIFICATION.
Auslieferungszustand: Sekundaersicherung in Vorraststellung.
Wenn nach Transport endverrastet oder herausgefallen, Nacharbeit
gemaess Verarbeitungs-Spezifikation erlaubt.
- 6
- MATCHING TO CONTACT E.G. TE NO. 2298488 AND 2298510
Passend zu Kontakt z.B. TE-Nr. 2298488 und 2298510
- 7
- CONDITION AS SUPPLIED: CPA IN PRE LOCKED POSITION
Auslieferungszustand: CPA in Vorraststellung
- 8
- TE ORDER NO. ACCORDING TABLE BELOW
TE Bestellnummer nach Tabelle unten
- 9
- SUITABLE MATING CONNECTOR TE-PN X-2310138-Y
Passender Anschlussstecker TE-PN X-2310138-Y
- 10
- CONFECTION TESTS COMBINED WITH CONTACT LEADS ARE TO BE MADE
WITH RF-ADAPTER 2318194-1
Konfektionspruefungen in Verbindung mit Leitungen sind mit
HF-Testadapter 2318194-1 durchzufuehren




EXPLODED VIEW
SCALE 2:1



CODINGS, PLUG SIDE, SIMILARITY AS VIEW SCALE 5:1
Kodierung, Steckseite, Darstellung der Kodierungen nur aehnlich

CODING A	CODING B	CODING C	CODING D	CODING E	CODING F	-
CODING G	CODING H	CODING J	CODING K	CODING L	CODING M	CODING Z

VARIANT 2 WITH CPA		2-2310137-x/ 3-2310137-x		SEE SHEET 2						
VARIANT 1 - WITHOUT CPA	1-2310137-9	B	1	Z	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	WATER BLUE		1	
	1-2310137-2	B	1	M	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	EMERALD GREEN		1	
	1-2310137-1	B	1	L	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	PASTEL GREEN		1	
	1-2310137-0	B	1	K	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	CURRY		1	
	2310137-9	B	1	J	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	BEIGE		1	
	2310137-8	B	1	N	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	HEATHER VIOLET		1	
	2310137-7	B	1	G	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	PLATINUM GREY		1	
	2310137-6	B	1	F	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	NUT BROWN		1	
	2310137-5	B	1	E	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	MAY GREEN		1	
	2310137-4	B	1	D	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	CLARET VIOLET		1	
	2310137-3	B	1	C	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	LIGHT BLUE		1	
	2310137-2	B	1	B	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	PURE WHITE		1	
	2310137-1	B	1	A	TPA	PA66-GF30	TRAFFIC PURPLE	0.75	2	
			1		HOUSING	PA66-GF30	JET BLACK		1	
VARIANT		TE ORDER NO.	REV.	QTY.	COD.	DESCRIPTION	MATERIAL	COLOUR	WEIGHT [g]	POS.
THIS DRAWING IS A CONTROLLED DOCUMENT.					DWN Nelson.R 18MAY2018 CHK M. Schoedel 18MAY2018 APVD E. Schrettlinger 21MAY2018		NAME 4POS. MATE-AX, SOC HSG ASSY, 180DEG 1pol. MATE-AX, Buchsengeh. Zsb, 180Grad			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES FINISH #H		APPLICATION SPEC 108-94709		SIZE CASE CODE DRAWING NO	
		WEIGHT -			116-94468		A 00779		RESTRICTED TO	
MATERIAL -					CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 2		REV B1	

