












REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APV	
A2		REMOVE PRELIMINARY WATERMARK	28AUG2019	CJ	CJ	
A3		REV PER ECO-21-005543	04MAR2021	CMJ	CMJ	
A4		ECN-22-144744	17MAR2022	SN	CJ	
A5		REV PER ECN-24-283739	17SEP2024	SMR	CS	

- 1 LASER MARK JULIAN DATE CODE APPROXIMATELY AS SHOWN.
- 2 CIRCUIT IDENTIFICATION.
3. MATING PART NUMBER: 2315564-1 THRU -4.
4. 1-2315562-1 SHOWN IN GENERAL VIEWS.
5. NOTE REMOVED.
6. NOTE REMOVED.
- 7 MATERIAL: BASE MATERIAL: BRASS.
PLATING: CONTACT AREA: 1.5-3.0 μ m TIN WITH
2.0 μ m MIN NICKEL UNDERPLATE.
SOLDER TAIL AREA: 2.5 μ m MIN TIN WITH
2.0 μ m MIN NICKEL UNDERPLATE.
- 8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 9 HOUSING MATERIAL: PA66-GF30.


10	10	10	10		PINS, 0.64X0.64	N/A	2
1	-	-	-		HOUSING, KEY D	BLUE	1
-	1	-	-		HOUSING, KEY C	GREEN	1
-	-	1	-		HOUSING, KEY B	GRAY	1
-	-	-	1		HOUSING, KEY A	TAN	1
1-2315562-4	1-2315562-3	1-2315562-2	1-2315562-1	MATERIAL	DESCRIPTION	COLOR	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE: 01MAY2017 DESIGNED BY: TISHA MINGO-ODUBOTE CHKD: 01MAY2017 APPROVED BY: RIDDHI KHIVRASARA 01MAY2017 GALEN MARTIN		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P/LC +.5 2 P/LC - 2 P/LC +0.13 3 P/LC +0.013 4 P/LC -0.0001 ANGLES .5		NAME: 10POS,TAB0.64X0.64,HDR ASSY, 180DEG,SLDR	
		PRODUCT SPEC: - APPLICATION SPEC: -		SIZE: - CAGE CODE: - DRAWING NO: - RESTRICTED: -	
MATERIAL: SEE TABLE		FINISH: - WEIGHT: 6.01g		A C=2315562	
CUSTOMER DRAWING		SCALE: 5:1		SHEET: 1 OF 2 REV: A5	


KEY	CODE	A







KEY CODE B




KEY CODE C



KEY CODE D



P		REVISIONS			
P	LYR	DESCRIPTION	DATE	DRN	APVD
-		SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 01MAY2017 TISHA MINGO-ODUBOTE CHK 01MAY2017 RIDDHI KHINVASA APVD 01MAY2017 GALEN MARTIN PRODUCT SPEC APPLICATION SPEC		 TE Connectivity 10POS, TAB0.64X0.64, HDR ASSY, 180DEG, SLDR	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC +0.00 1 PLC +0.00 2 PLC +0.00 3 PLC +0.013 4 PLC +0.0001 ANGLES 30°		NAME SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL SEE TABLE		FINISH WEIGHT 6.01g		A1 C=2315562 SCALE 5:1 SHEET 2 OF 2 REV A5	
		CUSTOMER DRAWING			