






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
AF	50	A	FIRST RELEASED	16AUG2019	WH	DZ	
		B	REVISED PER ECR-24-215168	04NOV2024	WH	LC	



NOTES:

- 1 MATERIAL:  
 HOUSING: NYLON 66, UL94V-0, COLOR NATURAL  
 TERMINAL: COPPER ALLOY, 2µm MIN TIN OVERALL
- 2 RECOMMENDED MATING PART: [J]-2323743-[]
- 3 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)



1.25	2	47.50	52.89	40	4-2323751-0		
0.00	2	45.00	50.39	38	3-2323751-8		
1.25	2	42.50	47.89	36	3-2323751-6		
0.00	2	40.00	45.39	34	3-2323751-4		
1.25	2	37.50	42.89	32	3-2323751-2		
0.00	2	35.00	40.39	30	3-2323751-0		
1.25	2	32.50	37.89	28	2-2323751-8		
0.00	2	30.00	35.39	26	2-2323751-6		
1.25	2	27.50	32.89	24	2-2323751-4		
0.00	2	25.00	30.39	22	2-2323751-2		
1.25	2	22.50	27.89	20	2-2323751-0		
0.00	2	20.00	25.39	18	1-2323751-8		
1.25	1	17.50	22.89	16	1-2323751-6		
0.00	1	15.00	20.39	14	1-2323751-4		
1.25	1	12.50	17.89	12	1-2323751-2		
0.00	1	10.00	15.39	10	1-2323751-0		
1.25	1	7.50	12.89	8	2323751-8		
DIM "M"	NO. OF LATCH CUT-OUTS	DIM "F"	DIM "L"	NO. OF POSITIONS	PART NO.		

2-2323751-0 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ±	APVD: DANIEL ZHANG 27AUG2018	NAME: DANIEL ZHANG
MATERIAL: 1	FINISH: -	PRODUCT SPEC: 108-2418	APPLICATION SPEC: 114-13315
		WEIGHT: -	SCALE: N/A

26AUG2018  
 DWN: WARREN HUO  
 27AUG2018  
 CHK: DANIEL ZHANG  
 27AUG2018  
 APVD: DANIEL ZHANG  
 27AUG2018

**STE** TE Connectivity


HEADER ASSEMBLY, EP2.5 DUAL ROW VERTICAL, WITHOUT BOSS, GWT

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-2323751 RESTRICTED TO: -


CUSTOMER DRAWING SHEET 1 OF 2 REV B

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
AF	50	-	SEE SHEET 1	-	-	




SINGLE LATCH DETAIL FOR  
2323751-8 AND 1-2323751-0




SINGLE LATCH DETAIL FOR  
1-2323751-2 THRU 1-2323751-6



DUAL LATCH DETAIL FOR  
1-2323751-8 THRU 4-2323751-0



RECOMMENDED PCB LAYOUT  
TOLERANCE: ±0.05



KINKED PIN CHART

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WARREN HUO 26AUG2018	TE Connectivity	
DIMENSIONS: mm		CHK DANIEL ZHANG 27AUG2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DANIEL ZHANG 27AUG2018	NAME HEADER ASSEMBLY, EP2.5 DUAL ROW VERTICAL, WITHOUT BOSS, GWT	
0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±5° FINISH		PRODUCT SPEC 108-2418	SIZE A200779	
MATERIAL 1 -		APPLICATION SPEC 114-13315	DRAWING NO C-2323751	
		WEIGHT -	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE N/A SHEET 2 OF 2 REV B	