







P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASED	29MAR21	V.L	E.J
B		ECR-21-004964	29APR21	V.L	E.J
B1		ECN-22-140986	24FEB22	V.L	E.J
B2		ECN-22-189690	08NOV22	V.L	E.J




-2 AS SHOWN
OTHER DIMENSIONS KEEP SAME WITH -1



SCALE 1:1
-1 AS SHOWN



SCALE 1:1
-2 AS SHOWN



- FOR DIMENSION / FEATURE NOT MENTIONED REFER TO 3D MODEL.
- COMPONENT APPEARANCE SHOULD REFER TO THE GOLDEN SAMPLE
NO SHRINKAGE-HOLE, CRACK OR DAMAGE PERMITTED
BURRS AT TOOL PARTING LINE MAX. 0.38 HIGH AND 0.1 WIDE PERMITTED
- STORAGE TEMPERATURE: -40~85°C
OPERATING TEMPERATURE: -40~125°C
- TE PN, 0.15mm MAX. RAISED
- MATERIAL MARKING ACC. TO VDA 260, 0.15mm MAX. RAISED
- TE LOGO, 0.15mm MAX. RAISED
- DATE CODE, 0.15mm MAX. RAISED
- MATED WITH TE PART: 2386359-X, 2386358-X, 2386365-1
- ALL PLASTIC PARTS MEET TESTS:
WITHDRAW VOLTAGE 3000V DC FOR 60s, LEAKAGE CURRENT<1mA
INSULATION RESISTANCE>500MΩ AT 500V DC FOR 60s

B2	3	ORANGE	PA66-GF30, V0	2386362-2
	2.9		PA66-GF30, V0	2386362-1
	WEIGHT (g)	COLOR	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16MAR2021	TE Connectivity NAME MTM PLUG HOUSING	
DIMENSIONS:		CHK	29MAR2021		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	29MAR2021		
	±0.3	F. JIANG			
	0 PLC ±	PRODUCT SPEC	TBD	SIZE	TBD
	1 PLC ±	APPLICATION SPEC	TBD	CAGE CODE	00779
	2 PLC ±	WEIGHT	-	DRAWING NO	C=2386362
	3 PLC ±	CUSTOMER DRAWING		RESTRICTED TO	-
	4 PLC ±			SCALE	2:1
	4 PLC ANGLES ±			SHEET	1 OF 1
MATERIAL	FINISH			REV	B2
PA66-GF30, V0	-				
ORANGE	-				