







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-18-011877	26JUL2018	DR	DR
	A1	ECO-18-014552	17SEP2018	DR	DR
	B	ECO-19-003684	11MAR2019	DR	DR



1. SUPPLY CONDITION: LEVER IN CLOSED POSITION
2. SUPPLY CONDITION: CPA IN CLOSED POSITION
3. LASER MARK DATE CODE YYDD HH:MM FORMAT
4. LASER MARK TE PART NUMBER
5. LASER MARK WORK CENTER
6. NOTE DELETED
7. DISCOLORATION ON THESE SURFACES DUE TO TRAPPED GAS IS PERMITTED
8. NONMETALLIC INCLUSIONS/SPECKS ARE PERMISSIBLE UP TO Ø1 IN MOLDED COMPONENTS



B	1	RED	PA66-GF35	CPA, WITH PUSH PAD	13
	1	BLACK	PA66-GF35	LEVER	12
	2	—	SEE DRAWING C-929454	MOS SOCKET CONTACT(X-928999-6)	11
	1	BLACK	PA66-GF35	FRONT SEAL RETAINER	10
	1	YELLOW	40 DUROMETER SILICONE, LUBRICATED	FRONT SEAL	9
	1	BLACK	PA66-GF35	REAR SEAL HOUSING	8
	1	BLUE	40 DUROMETER SILICONE, LUBRICATED	REAR SEAL	7
	1	—	CuNiSi PLATING: Ag OVER Ni	FERRULE SHIELD	6
	1	—	CuNiSi PLATING: Ag OVER Ni	LOWER SHIELD	5
	1	—	CuNiSi PLATING: Ag OVER Ni	PLUG SHIELD	4
	2	—	SS	TAB RETAINER	3
	1	NATURAL	PA66/6T-GF30-FR(40)	INNER HOUSING	2
	1	ORANGE	PA66-GF33	OUTER HOUSING	1
	1-2331152-1	COLOR	MATERIAL	DESCRIPTION	ITEM NO
	REVISION OF EACH ASSY NO (WHEN BLANK, USE DRAWING REVISION)				
	QTY REQ PER ASSY				
	PARTS LIST				
	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08FEB2018	TE Connectivity	
	DIMENSIONS:		CHK D. RHEIN 12FEB2018		
	mm		APVD D. RHEIN 12FEB2018	NAME	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	PLUG SUB-ASSEMBLY	
	0 PLC ±1.0		APPLICATION SPEC	HC-STAK 35-2PHI	
	1 PLC ±0.50		WEIGHT 267 g	SIZE CAGE CODE DRAWING NO	
	2 PLC ±		CUSTOMER DRAWING	A 00779C=2331152	
	3 PLC ±		SCALE 1:1	SHEET 1 OF 1	
	4 PLC ±		REV B		
	ANGLES ±4°				
	FINISH				