







P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL DRAWING	13OCT2022	AW	MM
	2	UPDATE TO ADD UL LOGO	05JAN2023	MM	MM
	A	ECR-23-167377	24FEB2023	RK	

PERFORMANCE REQUIREMENTS	
INPUT VOLTAGE RANGE	105-305VAC
INPUT FREQUENCY	50/60 Hz
LOAD RATINGS	TUNGSTEN: 1000W BALLAST: 1800VA ELECTRONIC BALLAST: 5A@277VAC
SURGE PROTECTION	445 JOULES, 15kA, 20mm MOV
OPERATING LIGHT LEVELS	1.5±0.5 Fc TURN ON,6.0 Fc MAX OFF
TIME DELAY ON/OFF	INSTANT ON,2-5 SECOND OFF
ON/OFF RATIO	1.5:1
FAIL MODE	ON
OPERATING TEMPERATURE	-40 TO 70°C
RELATIVE HUMIDITY	15 TO 96%,NON-CONDENSING ENVIRONMENT
STANDARDS	UL 773A ANSI C136.24

- NOTES:
1. MATERIALS AND FINISH: SEE TABLE
 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)

 PRODUCT INFORMATION LABEL



ALR-AA-2000EL	2393866-1
MODEL #	TE P/N

RED	16AWG STRD CU, 600V, 105°C,UL/AWM RATED	WIRE	8
WHITE	16AWG STRD CU, 600V, 105°C,UL/AWM RATED	WIRE	7
BLACK	16AWG STRD CU, 600V, 105°C,UL/AWM RATED	WIRE	6
BLACK	RUBBER	GASKET	5
BLACK	PPO	NUT	4
CLEAR	PC	LENS	3
BLACK	PC	TOP COVER	2
BLACK	PC	BOTTOM COVER	1
COLOR	MATERIAL		ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WESTBROOK CHK M. MOSTOLLER APVD -	TE Connectivity			
DIMENSIONS: mm		PRODUCT SPEC -	NAME PHOTOCONTROL, BUTTON STYLE ALR-AA-2000EL			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		APPLICATION SPEC 114-160404 WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-2393866	RESTRICTED TO -
MATERIAL SEE TABLE -		CUSTOMER DRAWING	SCALE 1:1	SHEET 1	OF 1	REV A