

4

3




2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	06AUG2018	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN
:CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS: 1.0~1.6±0.1



1.MATERIAL: HOUSING:GLASS FILED THERMO PLASTIC POLYESTER(94V-0),COLOR:BLACK
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

2.FINISH(ALL OVER):NICKEL PLATING 1.27umMIN.


3.FINISH(CONTACT AREA):GOLD PL. 0.38umMIN AFTER

4.FINISH(CONTACT TAIL):TIN PL. 2umMIN AFTER

5.THE SHAPE SIZE AND POSITION OF THE CHARACTER SHOW DETAILS



CONTACT TAIL
2 4



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 21-Aug-18														
DIMENSIONS: mm		CHK RICK.BIAN 21-Aug-18														
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±5°		APVD RICK.BIAN 21-Aug-18	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY 20POS TAIL LENGTH-5.0mm													
<table border="1"> <tr><td>Ø PLG</td><td>±</td></tr> <tr><td>1-PLG</td><td>±0.5</td></tr> <tr><td>2-PLG</td><td>±0.13</td></tr> <tr><td>3-PLG</td><td>±0.013</td></tr> <tr><td>4-PLG</td><td>±0.0001</td></tr> <tr><td>ANGLES</td><td>±</td></tr> </table>		Ø PLG	±	1-PLG	±0.5	2-PLG	±0.13	3-PLG	±0.013	4-PLG	±0.0001	ANGLES	±	PRODUCT SPEC 108-78268	SIZE A3	
Ø PLG	±															
1-PLG	±0.5															
2-PLG	±0.13															
3-PLG	±0.013															
4-PLG	±0.0001															
ANGLES	±															
MATERIAL SEE NOTE		APPLICATION SPEC 114-5377	CAGE CODE 00779	DRAWING NO C-2340037												
FINISH -		WEIGHT -	RESTRICTED TO -													
SEE NOTE		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1 REV A												