





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23AUG2023	R.C	Z.Z



- 1 MATERIAL: COPPER ALLOY 0.300 THICKNESS.
- 2 FINISH: OVERALL NICKEL 1.75 µm MINIMUM.
- 3. STRIP PARTS ARE REELED 3000 PARTS PER REEL.



INSULATION RANGE	WIRE RANGE	STAMP NO.	D	C	B	A	FINISH	MATERIAL	PART NUMBER
1.40mm-2.54mm	16-20 AWG	0.5-1.0	2.91	3.71	2.92	3.40	NICKEL 2	COPPER ALLOY	2500060-2
1.90mm-3.30mm	14-18 AWG	14-18 TW	3.27	3.95	3.38	4.56	NICKEL 2	COPPER ALLOY	2500060-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.CHEN 23AUG2023	TE Connectivity	
DIMENSIONS: mm		CHK C.WAN 23AUG2023		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.20		APVD Z.ZHOU 23AUG2023	NAME STAMPED CONTACT PIN SIZE 16	
1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ANGLES ±2.0°		PRODUCT SPEC 108-160783	RESTRICTED TO	
MATERIAL -		APPLICATION SPEC 114-160698	SIZE A2	CAGE CODE 00779
FINISH -		WEIGHT -	DRAWING NO. C-2500060	SCALE 5:1
		CUSTOMER DRAWING	SHEET 1 OF 1	REV A