



	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
-	A1	00779	C-2821988		
ER DRAWING			SCALE	SHEET	OF
			1:2	1	2
					REV B



- LABEL INFORMATION: -1 SHOWN



 -6 NET CABLE LENGHT 3 METERS REFERENCE.

6
5


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	160C12017
		SMITH	
		CHK	160C12017
		K. STAUFFER	
		APVD	-
		PRODUCT SPEC	
		APPLICATION SPEC	
		WEIGHT	-
		CUSTOMER DRAWING	

P3 QSFP-DD			P1 QSFP28	
GND	1		20	GND
TX2-	2	↔	21	RX2-
TX2+	3	↔	22	RX2+
GND	4		23	GND
TX4-	5	↔	24	RX4-
TX4+	6	↔	25	RX4+
GND	7		26	GND
ModseLL	8		27	ModPrsL
ResetL	9		28	intL
VccRx	10		29	VccTx
SCL	11		30	Vcc1
SDA	12		31	Reserved
GND	13		32	GND
RX3+	14	↔	33	TX3+
RX3-	15	↔	34	TX3-
GND	16		35	GND
RX1+	17	↔	36	TX1+
RX1-	18	↔	37	TX1-
GND	19		38	GND
GND	20		1	GND
RX2-	21	↔	2	TX2-
RX2+	22	↔	3	TX2+
GND	23		4	GND
RX4-	24	↔	5	TX4-
RX4+	25	↔	6	TX4+
GND	26		7	GND
ModPrsL	27		8	ModseLL
intL	28		9	ResetL
VccTx	29		10	VccRx
Vcc1	30		11	SCL
InitMode	31		12	SDA
GND	32		13	GND
TX3+	33	↔	14	RX3+
TX3-	34	↔	15	RX3-
GND	35		16	GND
TX1+	36	↔	17	RX1+
TX1-	37	↔	18	RX1-
GND	38		19	GND

P3 QSFP-DD			P2 QSFP28	
GND	39		20	GND
TX6-	40	↔	21	RX2-
TX6+	41	↔	22	RX2+
GND	42		23	GND
TX8-	43	↔	24	RX4-
TX8+	44	↔	25	RX4+
GND	45		26	GND
Reserved	46		27	ModPrsL
VS1	47		28	intL
VccRx1	48		29	VccTx
VS2	49		30	Vcc1
VS3	50		31	Reserved
GND	51		32	GND
RX7+	52	↔	33	TX3+
RX7-	53	↔	34	TX3-
GND	54		35	GND
RX5+	55	↔	36	TX1+
RX5-	56	↔	37	TX1-
GND	57		38	GND
GND	58		1	GND
RX6-	59	↔	2	TX2-
RX6+	60	↔	3	TX2+
GND	61		4	GND
RX8-	62	↔	5	TX4-
RX8+	63	↔	6	TX4+
GND	64		7	GND
NC	65		8	ModseLL
Reserved	66		9	ResetL
VccTx1	67		10	VccRx
Vcc2	68		11	SCL
Reserved	69		12	SDA
GND	70		13	GND
TX7+	71	↔	14	RX3+
TX7-	72	↔	15	RX3-
GND	73		16	GND
TX5+	74	↔	17	RX1+
TX5-	75	↔	18	RX1-
GND	76		19	GND

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 16OCT2017	TE Connectivity			
		CHK K. STAUFFER 16OCT2017				
DIMENSIONS:		mm  0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±	NAME CABLE ASSY, 28 AWG QSFP-DD TO (2) QSFP		RESTRICTED TO	
			SIZE CAGE CODE DRAWING NO			
			APPLICATION SPEC			
			WEIGHT			
MATERIAL		CUSTOMER DRAWING		SCALE 1:2	SHEET 2 OF 2	REV B