







REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
1		PROPOSED	24OCT2019	LS NR



00779, TE PART NO AND DATE CODE MARKED ON THIS SURFACE


6 POSITION
 2364119-1 THRU 2364119-2



00779, TE PART NO AND DATE CODE MARKED ON THIS SURFACE

7 POSITION
 2364119-3 THRU 2364119-4

- TE MATING CONNECTOR PART NUMBER 2360519 MATCHING KEYING AND NUMBER OF POSITIONS.
- SHELL FINISH: SELECTIVE PLATE 7.5µm MIN ZINC-NICKEL OVER 10.0µm MIN ELECTROLESS NICKEL ALL OVER.
- ROHS COMPLIANT.
- MATERIALS: ALUMINUM ALLOY, THERMOPLASTIC AND FLUORSILICONE.
- CONNECTOR SHALL MEET ENVIRONMENTAL REQUIREMENTS PER MIL-STD-810G.
- ASSEMBLY ACCEPTS SIZE 23 SOCKET CONTACTS.
- CONTACT CURRENT RATING 5 AMPS CRIMPED TO 22AWG WIRES.
- CONNECTOR SHIPPED WITH DUST CAPS.
- CONNECTOR WEIGHT: 4.39 grams (W/O CONTACTS).
- MARKINGS PER MIL-STD-202, METHOD 215.
- CONTACTS (8) ARE KITTED IN SEALED PLASTIC BAG AND SHIPPED UN-ASSEMBLED TO CONNECTOR.
- UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- THIS DRAWING HAS UNLIMITED USAGE RIGHTS.



POSITIONS	REMARKS	PART NO
7	---	2364119-4
7	△1	2364119-3
6	---	2364119-2
6	△1	2364119-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	LS	24OCT2019
CHK	N. RUFFINI	24OCT2019
APVD	N. RUFFINI	24OCT2019

TE Connectivity

RECEPTACLE CONNECTOR ASSEMBLY
 MASTER KEY ONLY
 NETT WARRIOR

SCALE 8:1 SHEET 1 OF 1 REV 1