





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	19DEC2023	KS	DZ




KEYING TYPE
(SCALE 3:1)



3-1376393-4	D	YELLOW	6	2371336-4
2-1376393-3	C	BLUE	6	2371336-3
1-1376393-2	B	VIOLET	6	2371336-2
1376393-1	A	NATURAL	6	2371336-1
2 MATING P/N	KEYING	COLOR	POS.	P/N

- 1 MATERIAL INFORMATION
HOUSING: HIGH TEMP NYLONCONFORMS TO UL-94 V0
GWEPT 750°C WITHOUT FLAME PER IEC 60335-1.
TAB CONTACT: COPPER ALLOY WITH TIN PLATED.
- 2 MATING PARTS: SEE TABLE.
- 3 CUIRUIT NUMBER.
- 4 TRADE MARK.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KEN SAKAI CHK DANIEL ZHANG APVD DANIEL ZHANG		10APR2023 10APR2023 10APR2023		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3		NAME HEADER ASSEMBLY 6P 5.0 POWER KEY CONNECTOR, SMT			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±3° FINISH		PRODUCT SPEC 108-106528 APPLICATION SPEC -		RESTRICTED TO -	
MATERIAL		-		WEIGHT 2.3g		SIZE A2	
CUSTOMER DRAWING		-		CAGE CODE 00779		DRAWING NO C=2371336	
				SCALE 5:1		SHEET 1 OF 2	
						REV A	




➡ USER DIRECTION OF UNREELING

D

C

B

A





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B

A



MYLAR FOR PICK AND PLACE

- NOTES FOR PACKAGE:
- UNLESS OTHERWISE SPECIFIED TOLERANCE PER EIA-481.
 - EMBOSS TAPE PEELING STRENGTH: 0.1N~1.3N
PEELING CONDITION
PEELING ANGLE: $165^{\circ} \sim 180^{\circ}$
PEELING SPEED: 300mm/MINUTE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KEN SAKAI	10APR2023	 TE Connectivity				
DIMENSIONS: mm		CHK DANIEL ZHANG	10APR2023					
		APVD DANIEL ZHANG	10APR2023	NAME HEADER ASSEMBLY 6P 5.0 POWER KEY CONNECTOR, SMT				
		PRODUCT SPEC 108-106528						
MATERIAL		APPLICATION SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO C-2371336	RESTRICTED TO -	
		WEIGHT -						
		CUSTOMER DRAWING				SCALE 4:1	SHEET 2 OF 2	REV A